


Price* : 138.00 USD

LX4FH375 has not been replaced. Please contact your customer care center for more information.



ⓘ Discontinued

Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX4FH
Range compatibility	TeSys F LC1F contactor
Product compatibility	LC1F265 LC1F330
Control circuit type	DC low consumption
[Uc] control circuit voltage	375 V DC
Average resistance	255 Ohm inrush at 68 °F (20 °C) 44000 Ohm holding at 68 °F (20 °C)
Inductance of closed circuit	7570 H
Operating time	40...50 ms closing 40...65 ms opening
Mechanical durability	10 Mcycles
Operating rate	<= 2400 cyc/h at <= 55 °C

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.15...0.2 Uc at 131 °F (55 °C) drop-out 0.85...1.1 Uc at 131 °F (55 °C) operational
Inrush power in W	750 W at 68 °F (20 °C)
Hold-in power consumption in W	5 W at 68 °F (20 °C)

Environment

Ambient air temperature for operation	> 23...131 °F (> -5...55 °C)
Product weight	1.63 lb(US) (0.74 kg)

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
Nbr. of units in pkg.	1
Package weight(Lbs)	1.8500000000000001

Returnability	N
---------------	---

Contractual warranty

Warranty period	18 months
-----------------	-----------
