

# Product data sheet

Specifications



## TeSys F - contactor coil - LX4FL - 75 V DC

LX4FL075

⚠ Discontinued

### Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LX4FL
Range Compatibility	TeSys TeSys F LC1F contactor
Product Compatibility	LC1F1250 LC1F630
Control Circuit Type	DC low consumption
[Uc] Control Circuit Voltage	75 V DC
Inductance Of Closed Circuit	180 H
Average Resistance	8.1 Ohm inrush 68 °F (20 °C) 1680 Ohm holding 68 °F (20 °C)
Operating Time	40...50 ms opening 60...70 ms closing
Mechanical Durability	5 Mcycles
Maximum Operating Rate	1200 cyc/h 131 °F (55 °C)

### Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Drop-out 0.2...0.35 Uc 131 °F (55 °C)) Operational 0.85...1.1 Uc 131 °F (55 °C))
Inrush Power In W	1600 W 68 °F (20 °C))
Hold-In Power Consumption In W	9 W 68 °F (20 °C)

### Environment

Ambient Air Temperature For Operation	23...131 °F (-5...55 °C)
Net Weight	3.20 lb(US) (1.45 kg)

### Ordering and shipping details

Category	22341-CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
Gtin	3389118113770
Returnability	No
Country Of Origin	FR

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

## Contractual warranty

Warranty	18 months
----------	-----------