

Product data sheet

Specifications



Multi9 - C60H - MCB - 1P - 50 A - C Curve - 240 V - 15 kA

M9F14150

⚠ Discontinued

Main

Range	Multi9
Product Name	Multi9 C60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	C60H
Device Application	Distribution
Poles Description	1P
Number Of Protected Poles	1
Line Rated Current	50 A 122 °F (50 °C) EN/IEC 60947-2
Network Type	AC DC
Trip Unit Technology	Thermal-magnetic
Curve Code	C
Breaking Capacity	20 kA Icu <= 72 V DC EN/IEC 60947-2 3 kA Icu 415 V AC 50/60 Hz between phase and neutral EN/IEC 60947-2 15 kA Icu 240 V AC 50/60 Hz between phase and neutral EN/IEC 60947-2
Utilisation Category	Category A EN/IEC 60947-2
Suitability For Isolation	Yes EN/IEC 60947-2
Standards	EN/IEC 60947-2
Product Certifications	EAC

Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	240 V AC 50/60 Hz between phase and neutral 415 V AC 50/60 Hz between phase and neutral <= 72 V DC
Magnetic Tripping Limit	8.5 x In +/- 20 % AC 12 x In +/- 20 % DC
[Ics] Rated Service Breaking Capacity	7.5 kA 50 % EN/IEC 60947-2 - 240 V AC 50/60 Hz 1.5 kA 50 % EN/IEC 60947-2 - 415 V AC 50/60 Hz 20 kA 100 % EN/IEC 60947-2 - <= 72 V DC
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz EN/IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	6 kVEN/IEC 60947-2
Contact Position Indicator	Yes
Control Type	Toggle

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Local Signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	2
Height	3.19 in (81 mm)
Width	0.71 in (18 mm)
Depth	2.83 in (72 mm)
Net Weight	0.26 lb(US) (0.12 kg)
Color	Gray
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles
Provision For Padlocking	Padlockable
Connections - Terminals	Tunnel type terminal top or bottom) 0.00...0.05 in² (1.5...35 mm²) - rigid Tunnel type terminal top or bottom) 0.00...0.05 in² (1.5...35 mm²) - flexible Tunnel type terminal top or bottom) 0.00...0.05 in² (1.5...35 mm²) - flexible with ferrule
Wire Stripping Length	0.55 in (14 mm) for top or bottom connection
Tightening Torque	30.98 lbf.in (3.5 N.m) top or bottom
Earth-Leakage Protection	Separate block

Environment

Heat Dissipation	4.8 W 240 V - 50 A
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	3 EN/IEC 60947-2
Overvoltage Category	IV
Tropicalisation	2 IEC 60068-1
Relative Humidity	95 % 131 °F (55 °C)
Ambient Air Temperature For Operation	-22...158 °F (-30...70 °C)
Ambient Air Temperature For Storage	-40...176 °F (-40...80 °C)

Ordering and shipping details

Gtin	3606480929892
------	---------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.95 in (7.5 cm)
Package 1 Width	0.71 in (1.8 cm)
Package 1 Length	3.35 in (8.5 cm)
Package 1 Weight	0.27 lb(US) (0.121 kg)