# **Product data sheet**

Specifications

Green Premium<sup>®</sup>



() Discontinued

### Miniature circuit breaker (MCB), Multi9 C60H, 3P, 4A, C curve, 15kA (IEC/EN 60947-2)

M9F14304

Discontinued on: Jan 31, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Range	Multi9
Product Name	Multi9 C60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	С60Н
Device Application	Distribution
Poles Description	3P
Number Of Protected Poles	3
Line Rated Current	4 A 122 °F (50 °C) EN/IEC 60947-2
Network Type	AC DC
Trip Unit Technology	Thermal-magnetic
Curve Code	C
Breaking Capacity	40 kA Icu <= 125 V DC EN/IEC 60947-2 30 kA Icu 240 V AC 50/60 Hz between phases EN/IEC 60947-2 15 kA Icu 415 V AC 50/60 Hz between phases EN/IEC 60947-2 10 kA Icu 440 V AC 50/60 Hz between phases EN/IEC 60947-2
Utilisation Category	Category A EN/IEC 60947-2
Suitability For Isolation	Yes EN/IEC 60947-2
Standards	EN/IEC 60947-2
Product Certifications	EAC CCC

#### Complementary

Network Frequency	50/60 Hz	
[Ue] Rated Operational Voltage	240 V AC 50/60 Hz between phases 415 V AC 50/60 Hz between phases 440 V AC 50/60 Hz between phases <= 125 V DC	
Magnetic Tripping Limit	8.5 x ln +/- 20 % AC 12 x ln +/- 20 % DC	
[Ics] Rated Service Breaking Capacity	15 kA 50 % EN/IEC 60947-2 - 240 V AC 50/60 Hz 7.5 kA 50 % EN/IEC 60947-2 - 415 V AC 50/60 Hz 5 kA 50 % EN/IEC 60947-2 - 440 V AC 50/60 Hz 40 kA 100 % EN/IEC 60947-2 - <= 125 V DC	
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz EN/IEC 60947-2	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

[Uimp] Rated Impulse Withstand Voltage	6 kVEN/IEC 60947-2	
Contact Position Indicator	Yes	
Control Type	Toggle	
Local Signalling	ON/OFF indication	
Mounting Mode	Clip-on	
Mounting Support	DIN rail	
9 Mm Pitches	6	
Height	3.19 in (81 mm)	
Width	2.13 in (54 mm)	
Depth	2.83 in (72 mm)	
Net Weight	0.79 lb(US) (0.36 kg)	
Color	Gray	
Mechanical Durability	20000 cycles	
Electrical Durability	10000 cycles	
Provision For Padlocking	Padlockable	
Connections - Terminals	Tunnel type terminal top or bottom) 0.000.04 in² (125 mm²) - rigid Tunnel type terminal top or bottom) 0.000.04 in² (125 mm²) - flexible Tunnel type terminal top or bottom) 0.000.04 in² (125 mm²) - flexible with ferrule	
Wire Stripping Length	0.55 in (14 mm) for top or bottom connection	
Tightening Torque	17.70 lbf.in (2 N.m) top or bottom	
Earth-Leakage Protection	Separate block	

#### Environment

Heat Dissipation	7.2 W 415 V - 4 A
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	3 EN/IEC 60947-2
Overvoltage Category	IV
Tropicalisation	2 IEC 60068-1
Relative Humidity	95 % 131 °F (55 °C)
Ambient Air Temperature For Operation	-22158 °F (-3070 °C)
Ambient Air Temperature For Storage	-40176 °F (-4080 °C)

# Ordering and shipping details

Category	US10DE200908	
Discount Schedule	0DE2	
Gtin	3606480577277	
Returnability	No	
Country Of Origin	FR	

## **Packing Units**

Unit Type Of Package 1

PCE

Number Of Units In Package 1	1	
Package 1 Height	2.13 in (5.4 cm)	
Package 1 Width	2.95 in (7.5 cm)	
Package 1 Length	3.35 in (8.5 cm)	
Package 1 Weight	11.43 oz (324 g)	
Unit Type Of Package 2	BB1	
Number Of Units In Package 2	4	
Package 2 Height	3.15 in (8 cm)	
Package 2 Width	3.54 in (9 cm)	
Package 2 Length	8.66 in (22 cm)	
Package 2 Weight	2.97 lb(US) (1.348 kg)	
Unit Type Of Package 3	S03	
Number Of Units In Package 3	48	
Package 3 Height	11.81 in (30 cm)	
Package 3 Width	11.81 in (30 cm)	
Package 3 Length	15.75 in (40 cm)	
Package 3 Weight	37.23 lb(US) (16.889 kg)	

Apr 25, 2024

### Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

Halogen Free Plastic Parts & Cables Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations