



Price\*\* : 287.00 USD

LX9FJ917 has not been replaced. Please contact your customer care center for more information.



⚠ Discontinued

## Main

Range	TeSys
Product or component type	Specific contactor coil
Device short name	LX9FJ
Range compatibility	TeSys F LC1F contactor TeSys F DR5TF rectifier
Product compatibility	LC1F400 DR5TF
Control circuit type	AC 40...400 Hz low consumption
[Uc] control circuit voltage	48 V AC 40...400 Hz 48 V DC
Average resistance	4.03 Ohm inrush at 68 °F (20 °C) 43 Ohm holding at 68 °F (20 °C)
Inductance of closed circuit	0.22 H
Operating time	60 ms opening 20 ms closing
Mechanical durability	10 Mcycles
Operating rate	<= 3600 cyc/h at <= 70 °C

## Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.3...0.5 Uc at 131 °F (55 °C) drop-out 0.85...1.1 Uc at 131 °F (55 °C) operational
Inrush power in VA	500 VA at 68 °F (20 °C) 40...400 Hz
Hold-in power consumption in VA	23 VA at 68 °F (20 °C) 40...400 Hz
Heat dissipation	11.4...13.9 W

## Environment

Ambient air temperature for operation	> 23...131 °F (> -5...55 °C)
---------------------------------------	------------------------------

Product weight	2.14 lb(US) (0.97 kg)
----------------	-----------------------

**Ordering and shipping details**

Category	18401 - WORLD SERVICE PARTS(CTR ACCESS)
Discount Schedule	CP10
Nbr. of units in pkg.	1
Package weight(Lbs)	2.5899999999999999
Returnability	N

**Offer Sustainability**

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0830 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Available

**Contractual warranty**

Warranty period	18 months
-----------------	-----------