

LX9FL923

specific contactor coil - TeSys F - 84..93 V DC - low consumption

Price** : 483.00 USD

LX9FL923 has not been replaced. Please contact your customer care center for more information.



⚠ Discontinued

Main

Range	TeSys
Product or component type	Specific contactor coil
Device short name	LX9FL
Range compatibility	TeSys F LC1F contactor
Product compatibility	LC1F630
Control circuit type	DC low consumption
[Uc] control circuit voltage	84...93 V DC
Operating time	60 ms opening 20 ms closing
Mechanical durability	5 Mcycles
Operating rate	<= 1800 cyc/h at <= 70 °C

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.3...0.5 Uc at 131 °F (55 °C) drop-out 0.85...1.1 Uc at 131 °F (55 °C) operational
Inrush power in W	733 W at 68 °F (20 °C)
Hold-in power consumption in W	48 W at 68 °F (20 °C)
Heat dissipation	22.8...27.8 W

Environment

Ambient air temperature for operation	> 23...131 °F (> -5...55 °C)
Product weight	3.2 lb(US) (1.45 kg)

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
Nbr. of units in pkg.	1
Package weight(Lbs)	3.1899999999999999
Returnability	N

Contractual warranty

Warranty period	18 months
-----------------	-----------
