

Product data sheet

Specifications



specific contactor coil - TeSys F - 300..334 V DC - low consumption

LX9FL934

⚠ Discontinued

Main

Range	TeSys
Product Or Component Type	Specific contactor coil
Device Short Name	LX9FL
Range Compatibility	TeSys TeSys F LC1F contactor
Product Compatibility	LC1F630
Control Circuit Type	AC 40...400 Hz low consumption DC low consumption
[Uc] Control Circuit Voltage	300...334 V DC
Operating Time	60 ms opening 20 ms closing
Mechanical Durability	5 Mcycles
Maximum Operating Rate	1800 cyc/h 158 °F (70 °C)

Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Operational 0.85...1.1 Uc 131 °F (55 °C)) Drop-out 0.3...0.5 Uc 131 °F (55 °C))
Inrush Power In W	733 W 68 °F (20 °C))
Hold-In Power Consumption In W	48 W 68 °F (20 °C)
Heat Dissipation	22.8...27.8 W

Environment

Ambient Air Temperature For Operation	23...131 °F (-5...55 °C)
Net Weight	3.20 lb(US) (1.45 kg)

Ordering and shipping details

Category	22341-CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
Gtin	3389118111875
Returnability	No

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------