

LXD1M7

TeSys D - contactor coil - LXD1 - 220 V AC 50/60 Hz for 9... 38 A contactor

Product availability : Stock - Normally stocked in distribution facility



Price** : 27.50 USD



Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LXD1
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	220 V AC 50/60 Hz
Average resistance	515.4 Ohm 68 °F (20 °C)
Inductance of closed circuit	18 H
Product compatibility	CAD LC1D09...D38 LC1DT20...DT40
Mechanical durability	9 Mcycles
Maximum operating rate	3600 cyc/h 140 °F (60 °C)

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out 0.3...0.6 Uc 50/60 Hz 140 °F (60 °C)) Operational 0.8...1.1 Uc 50 Hz 140 °F (60 °C)) Operational 0.85...1.1 Uc 60 Hz 140 °F (60 °C))
Inrush power in VA	70 VA 60 Hz 0.75 68 °F (20 °C)) 70 VA 50 Hz 0.75 68 °F (20 °C))
Hold-in power consumption in VA	7.5 VA 60 Hz 0.3 68 °F (20 °C)) 7 VA 50 Hz 0.3 68 °F (20 °C))
Heat dissipation	2...3 W 50/60 Hz

Environment

Ambient air temperature for operation	23... 140 °F (-5...60 °C)
Net weight	0.15 lb(US) (0.07 kg)

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901467892
Package weight(Lbs)	0.07 kg (0.15 lb(US))
Returnability	Yes
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide which is known to the State of California to cause Carcinogen harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------