

# Product data sheet

Specifications



motion servo drive, Lexium 32, 3A,  
single phase, supply voltage 115  
to 230V, 0.5 to 1kW

LXM32SD18M2

Product availability: Stock - Normally stocked in distribution facility

Price\*: 1,477.44 USD

## Main

|                           |                                                                                                                                                                                       |
|---------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Range Of Product          | Lexium 32                                                                                                                                                                             |
| Product Or Component Type | Motion servo drive                                                                                                                                                                    |
| Device Short Name         | LXM32S                                                                                                                                                                                |
| Format Of The Drive       | Book                                                                                                                                                                                  |
| Phase                     | Single phase                                                                                                                                                                          |
| [Us] Rated Supply Voltage | 100...120 V - 15...10 %<br>200...240 V - 15...10 %                                                                                                                                    |
| Supply Voltage Limits     | 85...132 V<br>170...264 V                                                                                                                                                             |
| Supply Frequency          | 50/60 Hz - 5...5 %                                                                                                                                                                    |
| Network Frequency         | 47.5...63 Hz                                                                                                                                                                          |
| Emc Filter                | Integrated                                                                                                                                                                            |
| Continuous Output Current | 6 A 8 kHz                                                                                                                                                                             |
| Output Current 3S Peak    | 10 A 115 V 5 s<br>18 A 230 V 5 s                                                                                                                                                      |
| Maximum Continuous Power  | 800 W 115 V<br>1600 W 230 V                                                                                                                                                           |
| Nominal Power             | 0.5 kW 115 V 8 kHz<br>1 kW 230 V 8 kHz                                                                                                                                                |
| Line Current              | 9.9 A 74 % 115 V, with external line choke 2 mH<br>10.6 A 93 % 230 V, with external line choke 2 mH<br>8.5 A 147 % 115 V, without line choke<br>8.4 A 148 % 230 V, without line choke |

## Complementary

|                         |                                                               |
|-------------------------|---------------------------------------------------------------|
| Switching Frequency     | 8 kHz                                                         |
| Overvoltage Category    | III                                                           |
| Maximum Leakage Current | 30 mA                                                         |
| Output Voltage          | <= power supply voltage                                       |
| Electrical Isolation    | Between power and control                                     |
| Type Of Cable           | Single-strand IEC cable 122 °F (50 °C)) copper 90 °C XLPE/EPR |
| Electrical Connection   | Terminal 3 mm², AWG 12 PA/+, PBI, PBe)                        |
| Tightening Torque       | PA/+, PBI, PBe 4.43 lbf.in (0.5 N.m)                          |
| Discrete Input Number   | 2 capture                                                     |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                         |                                                                                      |
|-------------------------|--------------------------------------------------------------------------------------|
| Discrete Input Type     | Capture CAP                                                                          |
| Sampling Duration       | 0.25 ms                                                                              |
| Discrete Input Voltage  | 24 V DC capture                                                                      |
| Discrete Input Logic    | Positive compliment of STO_A, compliment of STO_B)< 5 V > 15 V EN/IEC 61131-2 type 1 |
| Response Time           | <= 5 ms compliment of STO_A, compliment of STO_B                                     |
| Discrete Output Number  | 3                                                                                    |
| Discrete Output Type    | Logic DO)24 V DC                                                                     |
| Discrete Output Voltage | <= 30 V DC                                                                           |
| Discrete Output Logic   | Positive or negative DO)EN/IEC 61131-2                                               |
| Contact Bounce Time     | <= 1 ms compliment of STO_A, compliment of STO_B                                     |
| Braking Current         | 50 mA                                                                                |
| Response Time On Output | 250 µs DO)discrete                                                                   |
| Safety Function         | STO (safe torque off), Integrated                                                    |
| Safety Level            | SIL 3 EN/IEC 61508                                                                   |
| Communication Interface | Modbus, Integrated<br>SERCOS III, Integrated                                         |
| Connector Type          | RJ45 (labelled CN7) Modbus                                                           |
| Commissioning Port      | 2-wire RS485 multidrop Modbus                                                        |
| Transmission Rate       | 9600, 19200, 38400 bps 131.23 ft (40 m) Modbus                                       |
| Number Of Addresses     | 1...247 Modbus                                                                       |
| Status Led              | 1 LED (Red) servo drive voltage                                                      |
| Signalling Function     | Display of faults 7 segments                                                         |
| Marking                 | CE                                                                                   |
| Operating Position      | Vertical +/- 10 degree                                                               |
| Product Compatibility   | Servo motor BMH 2.76 in (70 mm), 1                                                   |
| Width                   | 2.68 in (68 mm)                                                                      |
| Height                  | 10.63 in (270 mm)                                                                    |
| Depth                   | 9.33 in (237 mm)                                                                     |
| Net Weight              | 4.19 lb(US) (1.9 kg)                                                                 |

## Environment

|                                       |                                                          |
|---------------------------------------|----------------------------------------------------------|
| Electromagnetic Compatibility         | Conducted EMC EN 55011 class A group 1                   |
| Standards                             | EN/IEC 61800-3                                           |
| Product Certifications                | CSA                                                      |
| Ip Degree Of Protection               | IP20 conforming to EN/IEC 60529                          |
| Vibration Resistance                  | 1 gn 13...150 Hz)EN/IEC 60068-2-6                        |
| Shock Resistance                      | 15 gn 11 ms EN/IEC 60028-2-27                            |
| Pollution Degree                      | 2 EN/IEC 61800-5-1                                       |
| Environmental Characteristic          | Classes 3C1 IEC 60721-3-3                                |
| Relative Humidity                     | Class 3K3 (5 to 85 %) without condensation IEC 60721-3-3 |
| Ambient Air Temperature For Operation | 32...122 °F (0...50 °C) UL                               |

|                                     |                                         |
|-------------------------------------|-----------------------------------------|
| Ambient Air Temperature For Storage | -13...158 °F (-25...70 °C)              |
| Type Of Cooling                     | Integrated fan                          |
| Operating Altitude                  | <= 3280.84 ft (1000 m) without derating |

## Ordering and shipping details

|                   |               |
|-------------------|---------------|
| Category          | US1PC5118261  |
| Discount Schedule | PC51          |
| Gtin              | 3606480694752 |
| Returnability     | Yes           |
| Country Of Origin | ID            |

## Packing Units

|                              |                           |
|------------------------------|---------------------------|
| Unit Type Of Package 1       | PCE                       |
| Number Of Units In Package 1 | 1                         |
| Package 1 Height             | 4.17 in (10.6 cm)         |
| Package 1 Width              | 10.83 in (27.5 cm)        |
| Package 1 Length             | 12.99 in (33 cm)          |
| Package 1 Weight             | 5.47 lb(US) (2.482 kg)    |
| Unit Type Of Package 2       | S03                       |
| Number Of Units In Package 2 | 2                         |
| Package 2 Height             | 11.81 in (30 cm)          |
| Package 2 Width              | 11.81 in (30 cm)          |
| Package 2 Length             | 15.75 in (40 cm)          |
| Package 2 Weight             | 12.83 lb(US) (5.819 kg)   |
| Unit Type Of Package 3       | P06                       |
| Number Of Units In Package 3 | 16                        |
| Package 3 Height             | 31.50 in (80 cm)          |
| Package 3 Width              | 31.50 in (80 cm)          |
| Package 3 Length             | 23.62 in (60 cm)          |
| Package 3 Weight             | 118.86 lb(US) (53.916 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability



**Green Premium™** label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

 Mercury Free

 Rohs Exemption Information   [Yes](#)

 Pvc Free


## Certifications & Standards

|                           |                                                                                                                                                                                                                                                                                             |
|---------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Reach Regulation          | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                           |
| Eu Rohs Directive         | Pro-active compliance (Product out of EU RoHS legal scope)                                                                                                                                                                                                                                  |
| China Rohs Regulation     | <a href="#">China RoHS declaration</a>                                                                                                                                                                                                                                                      |
| Environmental Disclosure  | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                               |
| Weee                      | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.                                                                                                                                                                |
| Circularity Profile       | <a href="#">End of Life Information</a>                                                                                                                                                                                                                                                     |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |

Dimensions Drawings

Lexium 32 Servo Drive


Dimensions



Mounting and Clearance

Lexium 32 Motion Control Servo Drives

Mounting Recommendations



LXM32•U45M2, •U90M2 and LXM32•U60N4 servo drives are cooled by natural convection. LXM32•D18M2, •D30M2, LXM32 •D12N4, •D18N4, •D30N4 and •D72N4servo drives have an integrated fan. When installing the servo drive in the enclosure, follow the instructions below with regard to the temperature and protection index:

- Provide sufficient cooling of the servo drive
- Do not mount the servo drive near heat sources
- Do not mount the servo drive on flammable materials
- Do not heat the servo drive cooling air by currents of hot air from other equipment and components, for example from an external braking resistor
- Mount the servo drive vertically ( $\pm 10\%$ )
- If the servo drive is used above its thermal limits, control stops due to overtemperature

**NOTE:** For cables that are connected via the underside of the servo drive, a free space  $\geq 200$  mm/7.87 in. is required under the unit to comply with the bending radius of the connection cables.


| Ambient temperature | Mounting distances | Instructions to be followed                         |
|---------------------|--------------------|-----------------------------------------------------|
| 0°C...+ 50°C        | d $\geq 0$ mm      | –                                                   |
| + 50°C...+ 60°C     | d $\geq 0$ mm      | Reduce the output current by 2.2% per °C above 50°C |

**NOTE:** Do not use insulated enclosures, as they have a poor level of conductivity.

Recommendations for Mounting in an Enclosure

To ensure good air circulation in the servo drive:

- Fit ventilation grilles on the enclosure.
- Ensure that ventilation is adequate, otherwise install a forced ventilation unit with a filter.



- (1) Natural convection
- (2) Forced ventilation

- Any apertures and/or fans must provide a flow rate at least equal to that of the servo drive fans (refer to characteristics).
- Use special filters with IP 54 protection.

**Mounting in Metal Enclosure (IP 54 Degree of Protection)**

The servo drive must be mounted in a dust and damp proof enclosure in certain environmental conditions, such as dust, corrosive gases, high humidity with risk of condensation and dripping water, splashing liquid, etc. In these cases, Lexium 32 servo drives can be installed in an enclosure where the internal temperature must not exceed 60°C.