



Main

Range	PowerLogic
Device short name	ION7550
Product or component type	Energy and power quality meter

Complementary

Power quality analysis	<ul style="list-style-type: none"> Waveform capture Disturbance direction detection Compliance monitoring Dip and swell, transient Harmonic distortion Programmability (logic and math functions) Setpoint learning Voltage sag and swell detection Up to the 63rd harmonic
Device application	<ul style="list-style-type: none"> Tariff metering Co-generation and IPP monitoring Demand and power factor control Load curtailment Equipment monitoring and control Energy pulsing and totalisation Instrument transformer correction
Type of measurement	<ul style="list-style-type: none"> Apparent power total Apparent power per phase Active power total Active power per phase Reactive power total Reactive power per phase Voltage Current Frequency Power factor total Power factor per phase
Supply voltage	<ul style="list-style-type: none"> 85...240 V AC 47...63 Hz 110...300 V DC
Network frequency	60 Hz

Line Rated Current	5 A
Type of network	1P + N 3P 3P + N
Power consumption in VA	20 VA at 85...240 V AC <= 45 VA at 85...240 V DC 20 VA at 110...300 V <= 45 VA at 110...300 V
Display resolution	320 x 240 pixels QVGA
Display type	Backlit LCD
Sampling rate	256 samples/cycle
Measurement current	0...5 A
Input type	Current 0.005...20 A 0.002 Ohm
Measurement voltage	100...600 V AC phase to phase 57...347 V AC phase to neutral
Frequency measurement range	42...69 Hz
Number of inputs	8 digital 120 V DC
Measurement accuracy	0.2 % energy 0.1 % current 1...5 A 0.1 % voltage 57...288 V
Accuracy class	Class 0.2S energy conforming to IEC 62053-22
Number of outputs	3 relay 4 solid state
Communication port protocol	Telnet DNP3 : <= 115.2 kbits/s, ION : <= 115.2 kbits/s, Modbus : <= 115.2 kbits/s, Modbus master
Communication port support	Infrared RS485 terminal block RS485/RS232 SUB-D 9
Data recording	Data logs Event logs Min/max of instantaneous values Sequence of event recording Time stamping Trending/forecasting GPS synchronisation
Transmission rate	300...57600 bauds 300...115200 bauds <= 19200 bauds
Memory capacity	5 MB
Web services	Web server
Tamperproof of settings	Protected by access code

Environment

Electromagnetic compatibility	<ul style="list-style-type: none"> • susceptibility to electromagnetic fields, conforming to IEC 61000-4-3 • electrical fast transient/burst immunity test, conforming to IEC 61000-4-4 • 1.2/50 µs shock waves immunity test, conforming to IEC 61000-4-5 • electrostatic discharge, conforming to IEC 61000-4-2 • conducted and radiated emissions class B, conforming to CISPR 22
Mounting mode	Flush-mounted
Mounting support	Enclosure door
Type of installation	Indoor installation
Overvoltage category	III
IP degree of protection	IP30 back IEC 60529 IP50 front face IEC 60529
Relative humidity	5...95 %
Pollution degree	2
Ambient air temperature for operation	-4...158 °F (-20...70 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)

Operating altitude	0...6561.68 ft (0...2000 m)
Standards	IEC 61010-1
Width	7.56 in (192 mm)
Depth	6.85 in (174 mm)
Height	7.56 in (192 mm)
Product weight	4.19 lb(US) (1.9 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0801 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------