

# Product data sheet

## Characteristics

# M9F53363

Multi 9 - C60BPR - MCB - 3P - 63 A - D Curve -  
240 V - 10 kA - UL 489

Product availability : Stock - Normally stocked in distribution facility



### Main

Range	Multi 9
Product name	Multi 9 C60
Product or component type	Miniature circuit-breaker
Device short name	C60BPR
Device application	Distribution
Poles description	3P
Number of protected poles	3
[In] rated current	63 A at 77 °F (25 °C) conforming to EN/IEC 60947-2
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	D
Breaking capacity	Icu 6 kA at 440 V AC conforming to EN/IEC 60947-2 Icu 10 kA at 415 V AC conforming to EN/IEC 60947-2 Icu 20 kA at 240 V AC conforming to EN/IEC 60947-2 Icu 6 kA at 440 V AC conforming to GB 14048.2 Icu 10 kA at 415 V AC conforming to GB 14048.2 Icu 20 kA at 240 V AC conforming to GB 14048.2 AIR 10 kA at 240 V AC conforming to UL 489 AIR 10 kA at 240 V AC conforming to CSA C22.2 No 5
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Standards	UL 489 CSA C22.2 No 5 GB 14048.2 EN/IEC 60947-2
Product certifications	UL CSA CCC IEC

### Complementary

System Voltage	240 V AC 50/60 Hz 415 V AC 50/60 Hz 440 V AC 50/60 Hz
Magnetic tripping limit	12 x In +/- 20% AC
[Ics] rated service breaking capacity	4.5 kA 75 % x Icu at 440 V AC conforming to EN/IEC 60947-2 7.5 kA 75 % x Icu at 415 V AC conforming to EN/IEC 60947-2

15 kA 75 % x Icu at 240 V AC conforming to EN/IEC 60947-2  
 4.5 kA 75 % x Icu at 440 V AC conforming to GB 14048.2  
 7.5 kA 75 % x Icu at 415 V AC conforming to GB 14048.2  
 15 kA 75 % x Icu at 240 V AC conforming to GB 14048.2

[Ui] rated insulation voltage	500 V AC conforming to EN/IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-2
Contact position indicator	Yes
Control type	Toggle
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	6
Height	5 in (127 mm)
Width	2.13 in (54 mm)
Depth	2.83 in (72 mm)
Colour	Grey
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Provision for padlocking	Padlockable
Connections - terminals	Ring terminal, top or bottom
Tightening torque	17.7 lbf.in (2 N.m) (top or bottom)
Earth-leakage protection	Without

## Environment

IP degree of protection	IP40 modular enclosure conforming to IEC 60529 IP20 conforming to IEC 60529
Pollution degree	3 conforming to EN/IEC 60947-2
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % ( 131 °F (55 °C) )
Operating altitude	0...6561.68 ft (0...2000 m)
Ambient air temperature for operation	-22...158 °F (-30...70 °C)
Ambient air temperature for storage	-40...176 °F (-40...80 °C)

## Ordering and shipping details

Category	00949 - M9 GEN 2 CB UL489
Discount Schedule	DE2
GTIN	00785901136279
Nbr. of units in pkg.	1
Package weight(Lbs)	1.0600000000000001
Returnability	Y

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1719 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>