Product data sheet

Specification





Miniature circuit breaker (MCB), Multi9 C60BPR, 1P, 40A, Z curve, 10kA (UL489), 10kA (IEC/EN 60947-2)

M9F54140

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 126.00 USD

Main

Range	Multi9
Product Name	Multi9 C60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	C60BPR
Device Application	Distribution
Poles Description	1P
Number Of Protected Poles	1
Line Rated Current	40 A 77 °F (25 °C) EN/IEC 60947-2
Network Type	DC AC
Trip Unit Technology	Thermal-magnetic
	<u> </u>
Curve Code	Z
Breaking Capacity	3 kA lcu 415 V AC EN/IEC 60947-2
	10 kA lcu 240 V AC EN/IEC 60947-2
	20 kA lcu 60 V DC EN/IEC 60947-2
	3 kA lcu 415 V AC GB 14048.2
	10 kA Icu 240 V AC GB 14048.2
	20 kA Icu 60 V DC GB 14048.2
	10 kA AIR 60 V DC UL 489
	10 kA AIR 240 V AC UL 489
	10 kA AIR 120 V AC UL 489
	10 kA AIR 60 V DC CSA C22.2 No 5
	10 kA AIR 240 V AC CSA C22.2 No 5
	10 kA AIR 120 V AC CSA C22.2 No 5
Suitability For Isolation	Yes EN/IEC 60947-2
Standards	EN/IEC 60947-2
	GB 14048.2
	UL 489
	CSA C22.2 No 5
Product Certifications	IEC
	CCC
	CSA
	UL

Complementary

[Ue] Rated Operational Voltage 240 V AC 50/60 Hz 415 V AC 50/60 Hz 60 V DC

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



Magnetic Tripping Limit	3 x In +/- 20 % AC
	4.2 x ln +/- 20 % DC
[Ics] Rated Service Breaking Capacity	2.25 kA 75 % EN/IEC 60947-2 - 415 V AC 7.5 kA 75 % EN/IEC 60947-2 - 240 V AC 2.25 kA 75 % GB 14048.2 - 415 V AC 7.5 kA 75 % GB 14048.2 - 240 V AC 15 kA 75 % GB 14048.2 - 60 V DC 15 kA 75 % EN/IEC 60947-2 - 60 V DC
[Ui] Rated Insulation Voltage	500 V AC EN/IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	6 kVEN/IEC 60947-2
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	2
Height	5.00 in (127 mm)
Width	0.71 in (18 mm)
Depth	2.83 in (72 mm)
Color	Gray
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles
Provision For Padlocking	Padlockable
Connections - Terminals	Ring terminal top or bottom)
Tightening Torque	17.70 lbf.in (2 N.m) top or bottom
Earth-Leakage Protection	Without

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	3 EN/IEC 60947-2
Tropicalisation	2 IEC 60068-1
Relative Humidity	95 % 131 °F (55 °C)
Operating Altitude	06561.68 ft (02000 m)
Ambient Air Temperature For Operation	-22158 °F (-3070 °C)
Ambient Air Temperature For Storage	-40176 °F (-4080 °C)

Ordering and shipping details

Category	US10DE200949
Discount Schedule	0DE2
Gtin	3606481170583
Returnability	No
Country Of Origin	FR

Packing Units

r aciming Cimes	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.71 in (1.8 cm)
Package 1 Width	2.95 in (7.5 cm)
Package 1 Length	5.00 in (12.7 cm)
Package 1 Weight	5.47 oz (155.0 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	3.15 in (8.0 cm)
Package 2 Width	8.66 in (22.0 cm)
Package 2 Length	5.20 in (13.2 cm)
Package 2 Weight	4.27 lb(US) (1.935 kg)
Unit Type Of Package 3	S03
Number Of Units In Package 3	96
Package 3 Height	11.81 in (30.0 cm)
Package 3 Width	11.81 in (30.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	35.20 lb(US) (15.967 kg)

Sustainability Screen Premium*

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
⊘	Rohs Exemption Information	Yes
Ø	Halogen Free Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations