



Price\* : 218.00 USD



### Main

|                           |   |
|---------------------------|---|
| Range                     | Multi 9   |
| Product name              | Multi 9 C60   |
| Product or component type | Miniature circuit-breaker   |
| Device short name         | C60SP   |
| Device application        | Distribution  |
| Poles description         | 2P  |
| Number of protected poles | 2   |
| [In] rated current        | 13 A at 77 °F (25 °C) conforming to EN/IEC 60947-2  |
| Network type              | DC<br>AC  |
| Trip unit technology      | Thermal-magnetic  |
| Curve code                | B   |
| Breaking capacity         | AIR 14 kA at 240 V AC conforming to UL 1077<br>AIR 14 kA at 240 V AC conforming to CSA C22.2 No 235<br>AIR 10 kA at 480Y/277 V AC conforming to UL 1077<br>AIR 10 kA at 125 V DC conforming to UL 1077<br>AIR 10 kA at 480Y/277 V AC conforming to CSA C22.2 No 235<br>AIR 10 kA at 125 V DC conforming to CSA C22.2 No 235<br>Icu 6 kA at 440 V AC conforming to EN/IEC 60947-2<br>Icu 10 kA at 415 V AC conforming to EN/IEC 60947-2<br>Icu 20 kA at 240 V AC conforming to EN/IEC 60947-2<br>Icu 6 kA at 440 V AC conforming to GB 14048.2<br>Icu 10 kA at 415 V AC conforming to GB 14048.2<br>Icu 20 kA at 240 V AC conforming to GB 14048.2 |
| Suitability for isolation | Yes conforming to EN/IEC 60947-2  |
| Standards                 | UL 1077<br>GB 14048.2<br>EN/IEC 60947-2<br>CSA C22.2 No 235   |
| Product certifications    | CSA<br>CCC  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Complementary

|  |  |
|--|--|
| System Voltage                         | 240 V AC 50/60 Hz<br>415 V AC 50/60 Hz<br>440 V AC 50/60 Hz  |
| Magnetic tripping limit                | 5.7 x I <sub>n</sub> +/- 20% DC<br>4 x I <sub>n</sub> +/- 20% AC   |
| [Ics] rated service breaking capacity  | 4.5 kA 75 % x I <sub>cu</sub> at 440 V AC conforming to EN/IEC 60947-2<br>7.5 kA 75 % x I <sub>cu</sub> at 415 V AC conforming to EN/IEC 60947-2<br>15 kA 75 % x I <sub>cu</sub> at 240 V AC conforming to EN/IEC 60947-2<br>4.5 kA 75 % x I <sub>cu</sub> at 440 V AC conforming to GB 14048.2<br>7.5 kA 75 % x I <sub>cu</sub> at 415 V AC conforming to GB 14048.2<br>15 kA 75 % x I <sub>cu</sub> at 240 V AC conforming to GB 14048.2 |
| [Ui] rated insulation voltage          | 500 V AC conforming to EN/IEC 60947-2  |
| [Uimp] rated impulse withstand voltage | 6 kV conforming to EN/IEC 60947-2  |
| Contact position indicator             | Yes  |
| Control type                           | Toggle   |
| Local signalling                       | ON/OFF indication  |
| Mounting mode                          | Clip-on  |
| Mounting support                       | DIN rail   |
| 9 mm pitches                           | 4  |
| Height                                 | 3.19 in (81 mm)  |
| Width                                  | 1.42 in (36 mm)  |
| Depth                                  | 2.83 in (72 mm)  |
| Colour                                 | Grey   |
| Mechanical durability                  | 20000 cycles   |
| Electrical durability                  | 10000 cycles   |
| Provision for padlocking               | Padlockable  |
| Connections - terminals                | Tunnel type terminal, top or bottom flexible with ferrule wire(s) 0...0.02 in <sup>2</sup> (1...16 mm <sup>2</sup> ) max (AWG 18...AWG 8)<br>Tunnel type terminal, top or bottom rigid wire(s) 0...0.04 in <sup>2</sup> (1...25 mm <sup>2</sup> ) max (AWG 18...AWG 8)<br>Tunnel type terminal, top or bottom flexible wire(s) 0...0.02 in <sup>2</sup> (1...16 mm <sup>2</sup> ) max (AWG 18...AWG 8)                                     |
| Wire stripping length                  | 0.55 in (14 mm) (top or bottom)  |
| Tightening torque                      | 22.12 lbf.in (2.5 N.m) (top or bottom)   |
| Earth-leakage protection               | Without  |

## Environment

|                                       |  |
|---------------------------------------|--|
| IP degree of protection               | IP40 modular enclosure conforming to IEC 60529<br>IP20 conforming to IEC 60529 |
| Pollution degree                      | 3 conforming to EN/IEC 60947-2   |
| Tropicalisation                       | 2 conforming to IEC 60068-1  |
| Relative humidity                     | 95 % ( 131 °F (55 °C) )  |
| Operating altitude                    | 0...6561.68 ft (0...2000 m)  |
| Ambient air temperature for operation | -22...158 °F (-30...70 °C)   |
| Ambient air temperature for storage   | -40...176 °F (-40...80 °C)   |

## Ordering and shipping details

|                       |                                  |
|-----------------------|----------------------------------|
| Category              | 00948 - M9 GEN 2 CB UL1077 / IEC |
| Discount Schedule     | DE2                              |
| GTIN                  | 00785901742975                   |
| Nbr. of units in pkg. | 1                                |
| Package weight(Lbs)   | 1                                |
| Returnability         | Y                                |
| Country of origin     | FR                               |

## Offer Sustainability

|                                  |   |
|----------------------------------|---|
| Sustainable offer status         | Green Premium product   |
| RoHS (date code: YYWW)           | Compliant - since 1719 - Schneider Electric declaration of conformity<br><a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                |
| Product environmental profile    | Available   |
| Product end of life instructions | Need no specific recycling operations   |