

Product data sheet

Characteristics

M9U21201

Multi 9 - C60H-DC - MCB - 2P - 1 A - C Curve -
500 V DC - 10 kA

Product availability : Stock - Normally stocked in distribution facility

Price* : 392.00 USD



Main

Range	Multi 9
Product name	Multi 9 C60H-DC
Product or component type	Miniature circuit-breaker
Device short name	C60H-DC
Device application	Distribution
Poles description	2P
Number of protected poles	2
[In] rated current	1 A at 77 °F (25 °C) conforming to EN/IEC 60947-2
Network type	DC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	Icu 20 kA at 220 V DC conforming to EN/IEC 60947-2 Icu 10 kA at 440 V DC conforming to EN/IEC 60947-2 Icu 6 kA at 500 V DC conforming to EN/IEC 60947-2 AIR 5 kA at 12...500 V DC conforming to UL 1077 Icu 20 kA at 220 V DC conforming to GB 14048.2 Icu 10 kA at 440 V DC conforming to GB 14048.2 Icu 6 kA at 500 V DC conforming to GB 14048.2
Utilisation category	Category A conforming to EN/IEC 60947-2
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Standards	UL 1077 GB 14048.2 EN/IEC 60947-2
Product certifications	CCC IEC UR

Complementary

System Voltage	220 V DC 440 V DC 500 V DC
Magnetic tripping limit	7...10 x In DC
[Ics] rated service breaking capacity	7.5 kA 75 % x Icu at 440 V DC conforming to EN/IEC 60947-2 4.5 kA 75 % x Icu at 500 V DC conforming to EN/IEC 60947-2

15 kA 75 % x Icu at 220 V DC conforming to EN/IEC 60947-2
 7.5 kA 75 % x Icu at 440 V DC conforming to GB 14048.2
 4.5 kA 75 % x Icu at 500 V DC conforming to GB 14048.2
 15 kA 75 % x Icu at 220 V DC conforming to GB 14048.2

[Ui] rated insulation voltage	500 V 500 V EN/IEC 60947-2 conforming to EN/IEC 60947-2 conforming to EN/IEC 60947-2 conforming to EN/IEC 60947-2 conforming to EN/IEC 60947-2 conforming to EN/IEC 60947-2 DC DC conforming to EN/IEC 60947-2 EN/IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-2
Contact position indicator	Yes
Control type	Toggle
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	4
Height	3.19 in (81 mm)
Width	1.42 in (36 mm)
Depth	2.87 in (73 mm)
Product weight	0.56 lb(US) (0.256 kg)
Colour	Grey
Mechanical durability	20000 cycles
Electrical durability	3000 cycles 250 V DC L/R = 2 ms 6000 cycles 250 V DC
Provision for padlocking	Padlockable
Connections - terminals	Tunnel type terminal, top or bottom rigid stranded wire(s) 0...0.04 in ² (1...25 mm ²) max (AWG 18...AWG 4) Tunnel type terminal, top or bottom flexible wire(s) 0...0.02 in ² (1...16 mm ²) max (AWG 18...AWG 6) Tunnel type terminal, top or bottom flexible with ferrule wire(s) 0...0.02 in ² (1...16 mm ²) max (AWG 18...AWG 6) Tunnel type terminal, top or bottom 2 rigid stranded wire(s) 0...0.02 in ² (1...10 mm ²) max (AWG 18...AWG 8) Tunnel type terminal, top or bottom 2 flexible wire(s) 0...0.02 in ² (1...10 mm ²) max (AWG 18...AWG 8) Tunnel type terminal, top or bottom 2 flexible with ferrule wire(s) 0...0.02 in ² (1...10 mm ²) max (AWG 18...AWG 8) Tunnel type terminal, top or bottom 3 flexible stranded wire(s) 0 in ² (1 mm ²) max (AWG 18)
Wire stripping length	0.55 in (14 mm) (top or bottom)
Tightening torque	22.12 lbf.in (2.5 N.m) (top or bottom)
Earth-leakage protection	Without

Environment

Heat dissipation	4.6 W 440 V 1 A
IP degree of protection	IP40 modular enclosure conforming to IEC 60529 IP20 conforming to IEC 60529
Pollution degree	3 conforming to EN/IEC 60947-2
Tropicalisation	2 conforming to IEC 60068-2 2 conforming to GB 14048.2
Relative humidity	95 % (131 °F (55 °C))
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)

Ordering and shipping details

Category	00948 - M9 GEN 2 CB UL1077 / IEC
Discount Schedule	DE2
GTIN	00785901775812
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5200000000000002
Returnability	Y
Country of origin	CN

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1645 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
