

# METSEEM3555

## PowerLogic EM3500 DIN rail meter - Modbus 4 quadrant - current transformer

Product availability : Non-Stock - Not normally stocked in distribution facility

Price\*\* : 940.00 USD



### Main

Range	PowerLogic
Range of product	PowerLogic EM3500
Device short name	EM3555
Product or component type	Energy meter
Metering type	Peak demand power PM, QM, SM Current I1, I2, I3, Iavg Active, reactive, apparent energy (signed, four quadrant) Demand power P, Q, S Voltage U21, U32, U13, V1, V2, V3

### Complementary

Poles description	3P + N
Type of measurement	Active and reactive power total Active and reactive power per phase Apparent power total Apparent power per phase Power factor total Power factor per phase Peak demand power Current Voltage Frequency
Device application	Partial meter Sub billing
Accuracy class	Class 0.2S power IEC 62053-22 Class 0.2S energy IEC 62053-22 Class 0.2S power ANSI C12.20 Class 0.2S energy ANSI C12.20
Measurement accuracy	Power +/- 0.2 % Energy +/- 0.2 %
Input type	split core current transducer 0.333 V or 1 V
Rated voltage	90...347 V
Network frequency	60 Hz 50 Hz
Technology type	Electronic
Display type	Backlit LCD

Measurement current	5...32000 A
Display digits	5
Information displayed	Status and alert Communication with system Input/output status Error Tx activity Rx activity Instant power per usage
Tamperproof of settings	Protected by access code
Communication port protocol	Modbus RTU 1200...38400 bps - 2-wire
Communication port support	Screw terminal block RS485
Communication of data	Instantaneous and demand values Lifetime energy production
Communication service	Total cumulated active energy Total cumulated energy
Data recording	Energy consumption logs Time stamping
Demand intervals	External synchronisation to communication Fixed or rolling block
Local signalling	Red LED threshold reached Green flashing LED output signal
Number of outputs	1 alarm output 1 pulse
Buffer size	16-bit 10
Power consumption in W	3 W 300 V
Mounting mode	Clip-on By screws
Mounting support	DIN rail
Standards	CSA C22.2 No 14-05 UL 508 IEC 61010-1
Product certifications	CE IEC 61010 CULus UL 508

## Environment

Relative humidity	0...95 %
Ambient air temperature for operation	-22...158 °F (-30...70 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Color	Dark grey
9 mm pitches	12
Width	4.21 in (107 mm)
Height	3.58 in (91 mm)
Depth	2.32 in (59 mm)

## Ordering and shipping details

Category	09798 - POWERLOGIC EM3500 SERIES
Discount Schedule	PL1
GTIN	00785901488514
Package weight(Lbs)	3.63 kg (8 lb(US))
Returnability	Yes
Country of origin	US

## Offer Sustainability

EU RoHS Directive	Not compliant
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.

---

WEEE

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

---