



Price\*\* : 7,719.00 USD



### Main

Product or component type	Circuit breaker
Range of product	PowerPact M
Breaking capacity code	G
Trip unit technology	Electronic, basic, ET 1.0, LI

### Complementary

Current sensor rating range	700 A
Line Rated Current	700 A
[Ue] rated operational voltage	600 V AC
Mounting mode	Unit mount
Poles description	2P
Breaking capacity	65 kA 240 V AC 35 kA 480 V AC 18 kA 600 V AC
Continuous current rating	80 %
Electrical connection	Lugs load Lugs line
AWG gauge	AWG 3/0...500 kcmil aluminium/copper)3
Terminal identifier	AL800M23K
Tightening torque	442.54 lbf.in (50 N.m) 0.15...0.37 in <sup>2</sup> (95...240 mm <sup>2</sup> ) AWG 3/0...500 kcmil)

### Environment

Product certifications	CSA IEC UL listed
------------------------	-------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Ordering and shipping details

Category	01205-MG, MJ UNIT MOUNT BREAKER
Discount Schedule	DE2
GTIN	00785901507611
Package weight(Lbs)	28.00 lb(US) (12.701 kg)
Returnability	Yes
Country of origin	US

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------