# Product data sheet

Specifications





## servo motor MH3 070 1,4Nm,no key,single16 lines,no brake,IP65/ IP67,6kRPM

MH30701P06F2200

! Discontinued on: Sep 30, 2023

! To be end-of-service on: Mar 31, 2025

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

· · · · · · · · · · · · · · · · · · ·	
Range Compatibility	PacDrive 3
Product Or Component Type	AC servo motors
Device Short Name	MH3

### Complementary

Maximum Mechanical Speed	8000 rpm	
[Us] Rated Supply Voltage	115480 V	
Phase	Three phase	
Continuous Stall Current	1.78 A	
Continuous Stall Torque	12.39 lbf.in (1.4 N.m), 115480 V, three phase	
Continuous Power	930 W	
Peak Stall Torque	37.17 lbf.in (4.2 N.m), 115480 V, three phase	
Nominal Output Power	0.18 W, 115 V 0.42 W, 230 V 0.75 W, 400 V 0.93 W, 480 V	
Nominal Torque	12.21 lbf.in (1.38 N.m) LXM52 1.75 mA, 115 V, 1 phase 11.86 lbf.in (1.34 N.m) LXM52 1.75 mA, 230 V, 1 phase 11.51 lbf.in (1.3 N.m) LXM52 1.72 mA, 400 V, 3 phase 11.24 lbf.in (1.27 N.m) LXM52 1.7 mA, 480 V, 3 phase 12.21 lbf.in (1.38 N.m) LXM62 1.75 mA, 115 V, 1 phase 11.86 lbf.in (1.34 N.m) LXM62 1.75 mA, 230 V, 1 phase 11.51 lbf.in (1.3 N.m) LXM62 1.72 mA, 400 V, 3 phase 11.24 lbf.in (1.27 N.m) LXM62 1.7 mA, 480 V, 3 phase	
Nominal Speed	1250 rpm LXM52 1.75 mA, 115 V, 1 phase 3000 rpm LXM52 1.75 mA, 230 V, 1 phase 5500 rpm LXM52 1.72 mA, 400 V, 3 phase 7000 rpm LXM52 1.7 mA, 480 V, 3 phase 1250 rpm LXM62 1.75 mA, 115 V, 1 phase 3000 rpm LXM62 1.75 mA, 230 V, 1 phase 5500 rpm LXM62 1.72 mA, 400 V, 3 phase 7000 rpm LXM62 1.77 mA, 480 V, 3 phase	
Maximum Current Irms	5.97 A	
Shaft End	Smooth shaft	
Second Shaft	Without second shaft end	
Shaft Diameter	0.43 in (11 mm)	
Shaft Length	0.91 in (23 mm)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ip Degree Of Protection	IP65 standard	
Encoder Type	Single turn SinCos Hiperface	
Speed Feedback Resolution	16 periods	
Holding Brake	With	
Holding Torque	26.55 lbf.in (3 N.m)	
Mounting Support	International standard flange	
Motor Flange Size	2.76 in (70 mm)	
Electrical Connection	Rotatable right-angled connectors	
Torque Constant	0.79 N.m/A 248 °F (120 °C)	
Back Emf Constant	50.72 V/krpm	
Number Of Motor Poles	10	
Rotor Inertia	0.7 kg.cm²	
Stator Resistance	8.28 Ohm	
Stator Inductance	23.4 mH	
Stator Electrical Time Constant	2.8 ms	
Maximum Radial Force Fr	660 N 1000 rpm 520 N 2000 rpm 460 N 3000 rpm 410 N 4000 rpm 380 N 5000 rpm 360 N 6000 rpm	
Brake Pull-In Power	7 W	
Type Of Cooling	Natural convection	
Length	6.34 in (161 mm)	
Centring Collar Diameter	2.36 in (60 mm)	
Centring Collar Depth	0.10 in (2.5 mm)	
Number Of Mounting Holes	4	
Mounting Holes Diameter	0.22 in (5.5 mm)	
Circle Diameter Of The Mounting Holes	3.23 in (82 mm)	
Net Weight	5.73 lb(US) (2.6 kg)	

# Ordering and shipping details

Category	US1PC5218359
Discount Schedule	PC52
Gtin	3606485394886
Returnability	No
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.53 in (11.5 cm)
Package 1 Width	7.48 in (19.0 cm)

Package 1 Length	15.55 in (39.5 cm)
Package 1 Weight	4.63 lb(US) (2.1 kg)

## Sustainability Screen Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov