# Product data sheet

Specifications





## Climasys CC - electronic hygrotherm - 95 to 135V - temp -40 to 80 C - Hr 20 to 80%

NSYCCOHYT120VID

Product availability: Stock - Normally stocked in distribution facility

### Price\*: 203.26 USD

### Overview

Lead Time

Usually Ships within 4 Weeks

#### Main

mann	
Range	ClimaSys
Product Name	ClimaSys CC
Product Or Component Type	Electronic hygrotherm
Temperature Setting Range	-40176 °F (-4080 °C)
Humidity Setting Range	2080 %
Display Type	OLED screen
Information Displayed	Temperature in °F Relative humidity Temperature in °C

### Complementary

Input Voltage	90140 V AC	
Sensor Type	Optional NTC external sensor	
Maximum Switching Capacity	4 A 120 V AC	
Electrical Connection	8 connectors 2.5 mm <sup>2</sup>	
Mounting Mode	By screws Clipped	
Height	External 3.35 in (85 mm)	
Width	External 2.20 in (56 mm)	
Depth	External 1.73 in (44 mm)	
Mounting Location	35mm DIN rail Cross rails On mounting plate Spacial upright	
Ambient Air Temperature For Operation	-40176 °F (-4080 °C)	
Hysteresis	2 K programmed value	
Hysteresis	3 %	
Number Of Outputs	2 ventilation/heating function	
Material	PC	
Color	Light gray	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Flame Retardance	
------------------	--

Product Certifications

# Ordering and shipping details

UR

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480152580
Returnability	Yes
Country Of Origin	US

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.30 in (5.842 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	3.40 in (8.636 cm)
Package 1 Weight	5.60 oz (158.759 g)

### **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Mercury Free

Rohs Exemption Information Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations