Product data sheet

Specification





ClimaSys CC - double thermostat 250V - range of temperature 0... 60°C - 1NO/NC - °C

NSYCCOTHD

Product availability: Stock - Normally stocked in distribution facility

Price*: 45.50 USD

Main

Range	ClimaSys
Product Name	ClimaSys CC
Product Or Component Type	Double thermostat
Temperature Setting Range	32140 °F (060 °C)
Information Displayed	Temperature in °C

Complementary

Input Voltage	250 V
Sensor Type	Bimetal
Contacts Type And Composition	1 NO/NC
Contact Resistance	10 mOhm
Service Life In Cycles	100000 cycles
Maximum Switching Capacity	2 A 120250 V AC inductive 0.6 10 A 250 V AC resistive 15 A 120 V AC resistive 30 W DC
Electrical Connection	4 terminals 2.5 mm²
Mounting Mode	Clipped
Height	External: 2.68 in (68 mm)
Width	External: 2.20 in (56 mm)
Depth	External 1.73 in (44 mm)
Net Weight	1.41 oz (40 g)
Mounting Location	Spacial upright On mounting plate 35 mm DIN rail Cross rails
Ambient Air Temperature For Operation	-4176 °F (-2080 °C)
Ip Degree Of Protection	IP20
Hysteresis	7 K +/- 0.4K
Number Of Outputs	1 heating function 1 ventilation function
Material	PC
Color	Light gray

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Flame Retardance	Self-extinguishing conforming to UL94 (material V0)
Product Certifications	UL

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480152511
Returnability	Yes
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.36 in (6 cm)
Package 1 Width	2.76 in (7 cm)
Package 1 Length	3.15 in (8 cm)
Package 1 Weight	3.67 oz (104 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations