Product data sheet

Specifications





Climasys Ultra thin resistance heater low starting current 50W 240V 200x320mm

NSYCRS50W240V

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 331.57 USD

Main

Range	ClimaSys
Product Name	ClimaSys CR
Product Or Component Type	Ultra thin resistance heater
Power Range	50 W
Input Voltage	240 V AC 50/60 Hz
Electrical Connection	Cable 6.56 ft (2 m)

Complementary

Operating Position	Vertical Horizontal
Ambient Air Temperature For Operation	-76158 °F (-6070 °C)
Temperature Setting Range	-40158 °F (-4070 °C)
Material	silicone rubber
Height	External 7.87 in (200 mm)
Width	External 12.60 in (320 mm)
Depth	External 0.06 in (1.6 mm)
Device Composition	6 self-adhesive Velcro pads 6 plastic spacers 4 Telequick nuts 4 clip-on nuts fixing accessories
Condition Of Use	Heaters must be installed with a thermal controller Electrical protection is needed Air sealed enclosure
Fixing Mode	By 4 screws
Mounting Support	Telequick mounting plate DIN rail Adhesive Velcro Standard mounting plate

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480530166
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin ES

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.97 in (5 cm)
Package 1 Width	12.80 in (32.5 cm)
Package 1 Length	13.78 in (35 cm)
Package 1 Weight	15.52 oz (440 g)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	180
Package 2 Height	70.87 in (180 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	47.24 in (120 cm)
Package 2 Weight	202.83 lb(US) (92 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations