

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Range	ClimaSys
Product name	CU
Product or component type	Cooling unit
Mounting type	Roof of enclosure
Type of installation	Indoor
Product destination	For enclosure
Mounting mode	By screws
Input voltage	230 V 50/60 Hz
Phase	1 phase
Cooling power	3920 Btu/h 50/60 Hz L35-L35 3070 Btu/h 50/60 Hz L35-L50

Complementary

Height	16.34 in (415 mm)
Width	567 mm
Depth	401 mm
Line Rated Current	3.2 A
Inrush current	11 A
Power consumption in W	550 W at 50/60 Hz, L35-L35 660 W at 50/60 Hz, L35-L50
Energy efficiency ratio	2.1
Control type	Electronic controller
Temperature setting range	68...122 °F (20...50 °C)
Ambient air temperature for operation	50 °C, maximum 20...46 °C, inside the enclosure 20...50 °C, outside the enclosure
Noise level	65 dB
Pressure	362.59 psi (25 bar)
Flow rate	Internal circuit : 570 m3/h at 50/60 Hz External circuit : 1010 m3/h at 50/60 Hz
Product weight	88.18 lb(US) (40 kg)
Cooling gas type	R134a (0.63 kg)

Type of filter	Optional external circuit filter
Protection type	Thermal protection: T 6 A Short-circuit protection (magnetic) :
Material	Steel
Colour	Grey RAL 7035

Environment

Product certifications	UL
Standards	DIN 3168
IP degree of protection	IP54 on the internal circuit conforming to IEC 60529 IP34 on the external circuit conforming to IEC 60529

Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	003606480654015
Nbr. of units in pkg.	1
Package weight(Lbs)	88.15999999999997
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov