
Product data sheet

Specifications



Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Side plate
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
Mounting Support	19" fixed rack, centred
Range Compatibility	Spacial Spacial SF Spacial Spacial SM
Device Composition	fixing elements 2 side plates
Quantity Per Set	Set of 1

Complementary

Material	steel
Color	Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By screws 19" fixed rack
Height	Nominal 55.12 in (1400 mm)
Width	Nominal 31.50 in (800 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480066726
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.77 in (4.5 cm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Width	4.13 in (10.5 cm)
Package 1 Length	51.57 in (131.0 cm)
Package 1 Weight	8.93 lb(US) (4.05 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations