

Product data sheet

Specifications



servo motor MH3 070
2,2Nm,key,multi 16
lines,brake,IP65/IP67,6kRPM

MH30702P17F2200

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 2,268.00 USD

Main

Range Compatibility	PacDrive 3
Product Or Component Type	AC servo motors
Device Short Name	MH3

Complementary

Maximum Mechanical Speed	8000 rpm
[Us] Rated Supply Voltage	115...480 V
Phase	Three phase
Continuous Stall Current	2.94 A
Continuous Stall Torque	21.95 lbf.in (2.48 N.m), 115...480 V, three phase
Continuous Power	1380 W
Peak Stall Torque	65.50 lbf.in (7.4 N.m), 115...480 V, three phase
Nominal Output Power	0.31 W, 115 V 0.7 W, 230 V 1.16 W, 400 V 1.38 W, 480 V
Nominal Torque	20.98 lbf.in (2.37 N.m) LXM52 2.82 mA, 115 V, 1 phase 19.74 lbf.in (2.23 N.m) LXM52 2.7 mA, 230 V, 1 phase 17.79 lbf.in (2.01 N.m) LXM52 2.49 mA, 400 V, 3 phase 16.73 lbf.in (1.89 N.m) LXM52 2.36 mA, 480 V, 3 phase 20.98 lbf.in (2.37 N.m) LXM62 2.82 mA, 115 V, 1 phase 19.74 lbf.in (2.23 N.m) LXM62 2.7 mA, 230 V, 1 phase 17.79 lbf.in (2.01 N.m) LXM62 2.49 mA, 400 V, 3 phase 16.73 lbf.in (1.89 N.m) LXM62 2.36 mA, 480 V, 3 phase
Nominal Speed	1250 rpm LXM52 2.82 mA, 115 V, 1 phase 3000 rpm LXM52 2.7 mA, 230 V, 1 phase 5500 rpm LXM52 2.49 mA, 400 V, 3 phase 7000 rpm LXM52 2.36 mA, 480 V, 3 phase 1250 rpm LXM62 2.82 mA, 115 V, 1 phase 3000 rpm LXM62 2.7 mA, 230 V, 1 phase 5500 rpm LXM62 2.49 mA, 400 V, 3 phase 7000 rpm LXM62 2.36 mA, 480 V, 3 phase
Maximum Current Irms	9.68 A
Shaft End	Parallel key
Second Shaft	Without second shaft end
Shaft Diameter	0.43 in (11 mm)
Shaft Length	0.91 in (23 mm)
Key Width	0.16 in (4 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ip Degree Of Protection	IP65 standard
Encoder Type	Multiturn SinCos Hiperface
Speed Feedback Resolution	16 periods
Holding Brake	With
Holding Torque	26.55 lbf.in (3 N.m)
Mounting Support	International standard flange
Motor Flange Size	2.76 in (70 mm)
Electrical Connection	Rotatable right-angled connectors
Torque Constant	0.84 N.m/A 248 °F (120 °C)
Back Emf Constant	54.08 V/krpm
Number Of Motor Poles	10
Rotor Inertia	1.24 kg.cm ²
Stator Resistance	3.84 Ohm
Stator Inductance	12.19 mH
Stator Electrical Time Constant	3.2 ms
Maximum Radial Force Fr	710 N 1000 rpm 560 N 2000 rpm 490 N 3000 rpm 450 N 4000 rpm 410 N 5000 rpm 390 N 6000 rpm
Brake Pull-In Power	7 W
Type Of Cooling	Natural convection
Length	7.60 in (193 mm)
Centring Collar Diameter	2.36 in (60 mm)
Centring Collar Depth	0.10 in (2.5 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.22 in (5.5 mm)
Circle Diameter Of The Mounting Holes	3.23 in (82 mm)
Net Weight	7.28 lb(US) (3.3 kg)

Ordering and shipping details

Category	US1PC5218359
Discount Schedule	PC52
Gtin	3606485395401
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.53 in (11.5 cm)
Package 1 Width	7.48 in (19.0 cm)

Package 1 Length	15.55 in (39.5 cm)
Package 1 Weight	5.07 lb(US) (2.3 kg)

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Pvc Free

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Circularity Profile

No need of specific recycling operations

California Proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov