

Product data sheet

Characteristics

NSYS3D6630P

Spacial S3D plain door with mount.plate.
H600xW600xD300.IP66 IK10 RAL7035.

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 222.43 USD



Main

Range	Spacial
Product name	Spacial S3D
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	23.62 in (600 mm)
Enclosure nominal width	23.62 in (600 mm)
Enclosure nominal depth	11.81 in (300 mm)
Door type	Plain
Mounting plate description	Plain
Type of gland plate	Standard
Installation accessory type	Wall-mounting
Device composition	Body 1 Mounting plate 1 Door with lock 1 Cable gland plate 1

Complementary

Body type	Single piece body Gutter-shaped front rail double sheet thickness
Number of doors	1 front face
Door opening side	Reversible 120 °
Lock type	3 points lock, 3 mm double-bar
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws Mounting plate by fixing element
Material	Galvanised steel mounting plate Steel enclosure

Surface finish	Epoxy-polyester powder enclosure
Colour	Grey RAL 7035 enclosure:
Standards	IEC 62208
Product certifications	LR CUL GL UL DNV BV
Product weight	46.3 lb(US) (21 kg)

Environment

IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	003606480159176
Nbr. of units in pkg.	1
Package weight(Lbs)	46.200000000000003
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0810 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------