Product data sheet

Specifications





servo motor MH3 100 3,3Nm,no key,single 16 lines,brake,IP65/ IP67,4kRPM

MH31001P06F2200

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 2,004.12 USD

Main

Range Compatibility	PacDrive 3	
Product Or Component Type	AC servo motors	
Device Short Name	MH3	

Complementary

Maximum Mechanical Speed	6000 rpm
[Us] Rated Supply Voltage	115480 V
Phase	Three phase
Continuous Stall Current	3.15 A
Continuous Stall Torque	30.09 lbf.in (3.4 N.m), 115480 V, three phase
Continuous Power	1520 W
Peak Stall Torque	95.59 lbf.in (10.8 N.m), 115480 V, three phase
Nominal Output Power	0.35 W, 115 V 0.67 W, 230 V 1.26 W, 400 V 1.52 W, 480 V
Nominal Torque	29.21 lbf.in (3.3 N.m) LXM52 3.07 mA, 115 V, 1 phase 28.32 lbf.in (3.2 N.m) LXM52 2.99 mA, 230 V, 1 phase 26.55 lbf.in (3 N.m) LXM52 2.83 mA, 400 V, 3 phase 25.67 lbf.in (2.9 N.m) LXM52 2.75 mA, 480 V, 3 phase 29.21 lbf.in (3.3 N.m) LXM62 3.07 mA, 115 V, 1 phase 28.32 lbf.in (3.2 N.m) LXM62 2.99 mA, 230 V, 1 phase 26.55 lbf.in (3 N.m) LXM62 2.83 mA, 400 V, 3 phase 25.67 lbf.in (2.9 N.m) LXM62 2.75 mA, 480 V, 3 phase
Nominal Speed	1000 rpm LXM52 3.07 mA, 115 V, 1 phase 2000 rpm LXM52 2.99 mA, 230 V, 1 phase 4000 rpm LXM52 2.83 mA, 400 V, 3 phase 5000 rpm LXM52 2.75 mA, 480 V, 3 phase 1000 rpm LXM62 3.07 mA, 115 V, 1 phase 2000 rpm LXM62 2.99 mA, 230 V, 1 phase 4000 rpm LXM62 2.83 mA, 400 V, 3 phase 5000 rpm LXM62 2.75 mA, 480 V, 3 phase
Maximum Current Irms	10.68 A
Shaft End	Smooth shaft
Second Shaft	Without second shaft end
Shaft Diameter	0.75 in (19 mm)
Shaft Length	1.57 in (40 mm)
Ip Degree Of Protection	IP65 standard

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Single turn SinCos Hiperface
16 periods
With
48.68 lbf.in (5.5 N.m)
International standard flange
3.94 in (100 mm)
Rotatable right-angled connectors
1.09 N.m/A 248 °F (120 °C)
70.3 V/krpm
10
3.68 kg.cm ²
4.12 Ohm
14.9 mH
4.5 ms
900 N 1000 rpm 720 N 2000 rpm 630 N 3000 rpm
570 N 4000 rpm 530 N 5000 rpm
•
530 N 5000 rpm
530 N 5000 rpm 12 W
530 N 5000 rpm 12 W Natural convection
530 N 5000 rpm 12 W Natural convection 6.70 in (170.3 mm)
530 N 5000 rpm 12 W Natural convection 6.70 in (170.3 mm) 3.74 in (95 mm)
530 N 5000 rpm 12 W Natural convection 6.70 in (170.3 mm) 3.74 in (95 mm) 0.14 in (3.5 mm)
530 N 5000 rpm 12 W Natural convection 6.70 in (170.3 mm) 3.74 in (95 mm) 0.14 in (3.5 mm) 4

Ordering and shipping details

Category	US1PC5218359	
Discount Schedule	PC52	
Gtin	3606485395845	
Returnability	No	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.27 in (21.0 cm)
Package 1 Width	7.09 in (18.0 cm)
Package 1 Length	14.02 in (35.6 cm)
Package 1 Weight	8.91 lb(US) (4.04 kg)

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov