Product data sheet





servo motor MH3 100 5,8Nm,no key,single 16 lines,brake,IP65/ IP67,4kRPM

MH31002P06F2200

! Discontinued on: Oct 9, 2023



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Compatibility	PacDrive 3	
Product Or Component Type	AC servo motors	
Device Short Name	MH3	

Complementary

Complemental y	
Maximum Mechanical Speed	6000 rpm
[Us] Rated Supply Voltage	115480 V
Phase	Three phase
Continuous Stall Current	5.04 A
Continuous Stall Torque	53.10 lbf.in (6 N.m), 115480 V, three phase
Continuous Power	2270 W
Peak Stall Torque	159.31 lbf.in (18 N.m), 115480 V, three phase
Nominal Output Power	0.59 W, 115 V 1.12 W, 230 V 1.95 W, 400 V 2.27 W, 480 V
Nominal Torque	50.18 lbf.in (5.67 N.m) LXM52 4.81 mA, 115 V, 1 phase 47.17 lbf.in (5.33 N.m) LXM52 4.58 mA, 230 V, 1 phase 41.33 lbf.in (4.67 N.m) LXM52 4.1 mA, 400 V, 3 phase 37.17 lbf.in (4.2 N.m) LXM52 3.73 mA, 480 V, 3 phase 50.18 lbf.in (5.67 N.m) LXM62 4.81 mA, 115 V, 1 phase 47.17 lbf.in (5.33 N.m) LXM62 4.58 mA, 230 V, 1 phase 41.33 lbf.in (4.67 N.m) LXM62 4.1 mA, 400 V, 3 phase 37.17 lbf.in (4.2 N.m) LXM62 3.73 mA, 480 V, 3 phase
Nominal Speed	1000 rpm LXM52 4.81 mA, 115 V, 1 phase 2000 rpm LXM52 4.58 mA, 230 V, 1 phase 4000 rpm LXM52 4.1 mA, 400 V, 3 phase 5000 rpm LXM52 3.73 mA, 480 V, 3 phase 1000 rpm LXM62 4.81 mA, 115 V, 1 phase 2000 rpm LXM62 4.58 mA, 230 V, 1 phase 4000 rpm LXM62 4.1 mA, 400 V, 3 phase 5000 rpm LXM62 3.73 mA, 480 V, 3 phase
Maximum Current Irms	17.4 A
Shaft End	Smooth shaft
Second Shaft	Without second shaft end
Shaft Diameter	0.75 in (19 mm)
Shaft Length	1.57 in (40 mm)
Ip Degree Of Protection	IP65 standard

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Encoder Type	Single turn SinCos Hiperface
Speed Feedback Resolution	16 periods
Holding Brake	With
Holding Torque	48.68 lbf.in (5.5 N.m)
Mounting Support	International standard flange
Motor Flange Size	3.94 in (100 mm)
Electrical Connection	Rotatable right-angled connectors
Torque Constant	1.19 N.m/A 248 °F (120 °C)
Back Emf Constant	78 V/krpm
Number Of Motor Poles	10
Rotor Inertia	6.77 kg.cm ²
Stator Resistance	1.97 Ohm
Stator Inductance	8.24 mH
Stator Electrical Time Constant	5 ms
Maximum Radial Force Fr	990 N 1000 rpm 790 N 2000 rpm 690 N 3000 rpm 620 N 4000 rpm 580 N 5000 rpm
Brake Pull-In Power	12 W
Type Of Cooling	Natural convection
Length	7.96 in (202.3 mm)
Centring Collar Diameter	3.74 in (95 mm)
Centring Collar Depth	0.14 in (3.5 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.35 in (9 mm)
Circle Diameter Of The Mounting Holes	4.53 in (115 mm)
Net Weight	14.11 lb(US) (6.4 kg)

Ordering and shipping details

Category	US1PC5218359
Discount Schedule	PC52
Gtin	3606485396163
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.27 in (21.0 cm)
Package 1 Width	7.09 in (18.0 cm)
Package 1 Length	14.02 in (35.6 cm)
Package 1 Weight	12.39 lb(US) (5.62 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov