


# NSYTRV22PE

Lineryg earth terminal block - 2.5mm<sup>2</sup> single-level  
1x1 screw - green-yellow

Product availability : Stock - Normally stocked in distribution facility



Price\*\* : 5.30 USD



## Main

Range	Lineryg
Product name	Lineryg TR
Product or component type	Terminal block
Device short name	TRV
Terminal block type	Protective earth
Terminal block level	1
Mounting mode	Clip-on
Nominal cross section	0 in <sup>2</sup> (2.5 mm <sup>2</sup> )
Length	1.88 in (47.7 mm)
Colour	Green-yellow
Quantity per set	Set of 50

## Complementary

Width	0.2 in (5.2 mm)
Height	1.87 in (47.5 mm)
Connections - terminals	1 x screw terminal : upstream 1 x screw terminal : downstream
Number of connections	2
Connection position	Sideways
Number of measurement input	2
Cable cross section	0.14...4 mm <sup>2</sup> , solid 0.2...2.5 mm <sup>2</sup> , flexible with cable end 0.14...4 mm <sup>2</sup> , flexible without cable end
Tightening torque	4.42...5.31 lbf.in (0.5...0.6 N.m)
Wire stripping length	0.35 in (9 mm)
Tool type	Connection : screwdriver Disconnection : screwdriver

Material	Polyamide 6/6 (insulating case)
Dielectric loss	0.01 at 1 MHz conforming to IEC 60250 0.01 at 1 MHz conforming to VDE 0303-T4
Dielectric constant	3.7 at 1 MHz
Resistivity	10000 M $\Omega$ .m conforming to IEC 60093 10000 M $\Omega$ .m conforming to VDE 0303-T30
Surface resistance	1000 G $\Omega$ conforming to IEC 60093 1000 G $\Omega$ conforming to VDE 0303-T30
Creep resistance	500 CTI (> 400 kV) conforming to IEC 60093 500 CTI (> 400 kV) conforming to VDE 0303-T30
Flame retardance	V0, thickness 0.03 in (0.8 mm) conforming to UL 94
Product weight	0.41 oz (11.58 g)
Range compatibility	Prisma - G Prisma - P Prisma - PH Prisma - Pack Spacial Kaedra TeSys
Product compatibility	Spacial enclosures

## Environment

Product certifications	DNV IEC-Ex ATEX cURus CSA GL LR EAC VDE
Dielectric strength	1000 V conforming to IEC 60243-1
Ambient air temperature for operation	-40...266 °F (-40...130 °C) conforming to IEC 60216-1 -40...266 °F (-40...130 °C) conforming to VDE 0304-T21

## Ordering and shipping details

Category	21715 - IEC TERMINAL BLOCKS-NSY,AM1,DF6,GK1
Discount Schedule	CP5
GTIN	00785901943402
Nbr. of units in pkg.	50
Package weight(Lbs)	2.999999999999999E-2
Returnability	Y
Country of origin	DE

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1052 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference contains SVHC above the threshold - Go to CaP for more details <a href="#">Go to CaP for more details</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---