Product data sheet

Specifications

SQUARE D

Green



Panelboard interior, NQ, main lugs, 400A, Cu bus, 42 pole spaces, 3 phase, 4 wire, 240VAC, 48VDC

NQ442L4C

Product availability: Stock - Normally stocked in distribution facility

Price*: 2,133.00 USD

Main

Panelboard Type	Main lugs
Product Or Component Type	Interiors
Branch Circuit Breaker Type	QOB QOB-VH QHB
Busbar Material	Copper

Complementary

Number Of Spaces	42	
Enclosure Nominal Height	50 in (1270.00 mm)	
Enclosure Nominal Width	20 in (508.00 mm)	
Enclosure Nominal Depth	5.75 in (146.05 mm) NEMA 1 6.5 in (165.10 mm) NEMA 3R/5/12	
Line Rated Current	400 A	
[lu] Rated Interrupted Current	10 kA 22 kA 65 kA	
Number Of Phases	3 phase 4 wires	
Voltage Rating	240 V AC 48 V DC	
Connections - Terminals	Lug line AWG 1/0750 kcmil aluminium Lug neutral AWG 1/0750 kcmil aluminium	
Tightening Torque	274.99300.04 lbf.in (31.0733.90 N.m) 0.080.59 in² (53.48380 mm²) (AWG 1/0750 kcmil) 274.99300.04 lbf.in (31.0733.90 N.m) 0.080.27 in² (53.48177.3 mm²) (AWG 1/0350 kcmil) 549.98 lbf.in (62.14 N.m) 0.080.59 in² (53.48380 mm²) (AWG 1/0750 kcmil) 549.98 lbf.in (62.14 N.m) 0.080.24 in² (53.48152 mm²) (AWG 1/0300 kcmil) 375.01 lbf.in (42.37 N.m) 0.080.59 in² (53.48380 mm²) (AWG 1/0750 kcmil) 375.01 lbf.in (42.37 N.m) 0.080.24 in² (53.48152 mm²) (AWG 1/0300 kcmil)	
Height	45 in (1143.00 mm)	
Width	10.44 in (265.18 mm)	
Net Weight	26.65 lb(US) (12.09 kg)	

Environment

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US1PE1A09151	
Discount Schedule	PE1A	
Gtin	785901507918	
Returnability	Yes	
Country Of Origin	US	

Packing Units

V	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.50 in (16.5 cm)
Package 1 Width	14.02 in (35.6 cm)
Package 1 Length	50.00 in (127.0 cm)
Package 1 Weight	21.75 lb(US) (9.866 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	15
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	42.00 in (106.68 cm)
Package 2 Length	60.00 in (152.4 cm)
Package 2 Weight	327.00 lb(US) (148.325 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance


Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Approximate Dimensions



* For Type 3R enclosure, increase height dimension by 12.00 / [305]