

Product data sheet

Specifications



ClimaSys indoor slim cooling unit block - 3200W at 460 V - UL

NSYCUS3K23P4UL

- Discontinued on:** Jul 27, 2023
- End-of-service on:** Dec 31, 2023

Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	ClimaSys
Product Name	CU
Product Or Component Type	Slim cooling unit block
Mounting Type	Door of enclosure
Installation	Indoor side
Product Destination	For enclosure
Mounting Mode	By screws
Supply Voltage	460 V AC 60 Hz, 3 phase
Rated Power	3200 W
Cooling Power	10919 Btu/h 60 Hz L35-L35 8530 Btu/h 60 Hz L35-L50

Complementary

Height	66.77 in (1696 mm)
Width	19.49 in (495 mm)
Depth	9.25 in (235 mm)
Line Rated Current	3.1 A
Inrush Current	18 A
Power Consumption In W	1650 W 60 Hz, L35-L35 1980 W 60 Hz, L35-L50
Energy Efficiency Ratio	1.9
Control Type	Electronic controller
Temperature Setting Range	68...122 °F (20...50 °C)
Ambient Air Temperature For Operation	Maximum 122 °F (50 °C) Inside the enclosure 68...115 °F (20...46 °C) Outside the enclosure 68...122 °F (20...50 °C)
Noise Level	69 dB EN/ISO 3746
Pressure	406.11 psi (28 bar)
Flow Rate	Internal circuit 383056.34 Gal/hr(US) (1450 m3/h) 60 Hz External circuit 383056.34 Gal/hr(US) (1450 m3/h) 60 Hz
Net Weight	176.37 lb(US) (80 kg)
Cooling Gas Type	R134a 2.76 lb(US) (1.25 kg))

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Type Of Filter	Optional external circuit filter
Protection Type	Thermal protection T 6 A Short-circuit protection (magnetic)
Material	Steel
Color	Gray RAL 7035)

Environment

Product Certifications	UL
Ip Degree Of Protection	IP55 IEC 60529 on the internal circuit) IP34 IEC 60529 on the external circuit)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480685767
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.68 in (19.5 cm)
Package 1 Width	19.49 in (49.5 cm)
Package 1 Length	66.77 in (169.6 cm)
Package 1 Weight	182.98 lb(US) (83.0 kg)
Unit Type Of Package 2	P12
Number Of Units In Package 2	2
Package 2 Height	81.10 in (206.0 cm)
Package 2 Width	31.50 in (80.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	478.40 lb(US) (217.0 kg)

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information