

# Product data sheet

Specifications



ION7550 - wDispl - 10MB 256s - 5A  
240VAC/300VDC 60Hz - RS+T2 -  
8I+3R+4O

P7550B0C0B6A0A0A

⚠ Discontinued on: Jun 1, 2021

⚠ Discontinued

## Main

Range	PowerLogic
Product Name	PowerLogic ION7550
Device Short Name	ION7550
Product Or Component Type	Energy and power quality meter

## Complementary

Power Quality Analysis	harmonic distortion compliance monitoring dip and swell, transient disturbance direction detection programmability (logic and math functions) setpoint learning voltage sag and swell detection waveform capture up to the 63rd harmonic
Device Application	Demand and power factor control Equipment monitoring and control Energy pulsing and totalisation Tariff metering Co-generation and IPP monitoring Load curtailment Instrument transformer correction
Type Of Measurement	Power factor total Power factor per phase Apparent power total Apparent power per phase Active power total Active power per phase Reactive power total Reactive power per phase Current Voltage Frequency
Supply Voltage	110...300 V DC 85...240 V AC 47...63 Hz
Network Frequency	60 Hz
Line Rated Current	5 A
Poles Description	3P + N 3P 1P + N
Power Consumption In Va	20 VA 85...240 V AC 20 VA 110...300 V DC
Maximum Power Consumption In Va	45 VA 85...240 V AC 45 VA 110...300 V DC

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Display Type	Backlit LCD
Sampling Rate	256 samples/cycle
Measurement Current	0...5 A
Input Type	Current 0.005...20 A (impedance 0.002 Ohm)
Measurement Voltage	100...600 V AC phase to phase 57...347 V AC phase to neutral
Frequency Measurement Range	42...69 Hz
Number Of Inputs	8 digital 120 V DC
Measurement Accuracy	Current 0.1 % 1...5 A Voltage 0.1 % 57...288 V Energy 0.2 %
Accuracy Class	Class 0.2S energy IEC 62053-22
Number Of Outputs	3 relay 4 solid state
Communication Port Protocol	Telnet DNP3 <= 115.2 kbits/s ION <= 115.2 kbits/s Modbus <= 115.2 kbits/s Modbus, master
Communication Port Support	SUB-D 9 RS485/RS232 infrared Terminal block RS485
Data Recording	Data logs Event logs Time stamping Min/max of instantaneous values Trending/forecasting GPS synchronisation Sequence of event recording
Transmission Rate	<= 19200 bauds 300...115200 bauds 300...57600 bauds
Memory Capacity	10 MB
Web Services	Web server
Tamperproof Of Settings	Protected by access code
Compatibility Code	ION7550

## Environment

Electromagnetic Compatibility	Electrostatic discharge conforming to IEC 61000-4-2 Susceptibility to electromagnetic fields conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test conforming to IEC 61000-4-4 1.2/50 µs shock waves immunity test conforming to IEC 61000-4-5 Conducted and radiated emissions B conforming to CISPR 22
Mounting Mode	Flush-mounted
Mounting Support	Enclosure door
Type Of Installation	Indoor installation
Overvoltage Category	III
Ip Degree Of Protection	IP30 back: conforming to IEC 60529 IP50 front face: conforming to IEC 60529
Relative Humidity	5...95 %
Pollution Degree	2
Ambient Air Temperature For Operation	-4...158 °F (-20...70 °C)

Ambient Air Temperature For Storage	-40...185 °F (-40...85 °C)
Operating Altitude	0...6561.68 ft (0...2000 m)
Standards	IEC 61010-1
Width	7.56 in (192 mm)
Depth	6.85 in (174 mm)
Height	7.56 in (192 mm)
Net Weight	4.19 lb(US) (1.9 kg)

## Ordering and shipping details

Category	09754-POWERLOGIC ION 75/76 HARDWARE
Discount Schedule	PM1
Returnability	No

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

California Proposition 65

WARNING: Cancer and Reproductive Harm - [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

---