

# Product data sheet

Specifications



ION7650 - wDispl - 10MB 1024s -  
5A 240VAC/300VDC 60Hz -  
RS+T2+E - 8I+3R+4O

P7650B1C0B6E0A0A

⚠ Discontinued on: Jun 1, 2021

⚠ Discontinued

## Main

Range	PowerLogic
Product Name	PowerLogic ION7650
Device Short Name	ION7650
Product Or Component Type	Energy and power quality meter

## Complementary

Power Quality Analysis	harmonic distortion compliance monitoring dip and swell, transient disturbance direction detection programmability (logic and math functions) setpoint learning voltage sag and swell detection waveform capture up to the 63rd harmonic
Device Application	Energy pulsing and totalisation Tariff metering Demand and power factor control Instrument transformer correction Co-generation and IPP monitoring Load curtailment Equipment monitoring and control
Type Of Measurement	Power factor total Power factor per phase Apparent power total Apparent power per phase Active power total Active power per phase Reactive power total Reactive power per phase Current Voltage Frequency
Supply Voltage	110...300 V DC 85...240 V AC 47...63 Hz
Network Frequency	60 Hz
Line Rated Current	5 A
Poles Description	1P + N 3P + N 3P
Power Consumption In Va	20 VA
Maximum Power Consumption In Va	45 VA
Display Resolution	320 x 240 pixels QVGA

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Display Type	Backlit LCD
Sampling Rate	1024 samples/cycle
Measurement Current	0...5 A
Input Type	Current 0.005...20 A (impedance 0.002 Ohm)
Measurement Voltage	100...600 V AC phase to phase 57...347 V AC phase to neutral
Frequency Measurement Range	42...69 Hz
Number Of Inputs	8 digital 120 V DC
Measurement Accuracy	Current 0.1 % 1...5 A Voltage 0.1 % 57...288 V Energy 0.2 %
Accuracy Class	Class 0.2S energy IEC 62053-22
Number Of Outputs	3 relay 4 solid state
Communication Port Protocol	Telnet DNP3 <= 115.2 kbits/s ION <= 115.2 kbits/s Modbus <= 115.2 kbits/s TCP/IP 10/100 Mbit/s
Communication Port Support	SUB-D 9 RS232 ST fiber optic RJ11 modem RJ45 ETHERNET RS485
Data Recording	Data logs Time stamping Sequence of event recording Trending/forecasting Event logs GPS synchronisation Min/max of instantaneous values
Transmission Rate	<= 19200 bauds 10/100 Mbit/s 300...57600 bauds 300...115200 bauds
Memory Capacity	10 MB
Web Services	Web server
Tamperproof Of Settings	Protected by access code
Compatibility Code	ION7650

## Environment

Electromagnetic Compatibility	Electrostatic discharge conforming to IEC 61000-4-2 Susceptibility to electromagnetic fields conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test conforming to IEC 61000-4-4 1.2/50 µs shock waves immunity test conforming to IEC 61000-4-5 Conducted and radiated emissions B conforming to CISPR 22
Mounting Mode	Flush-mounted
Mounting Support	Enclosure door
Type Of Installation	Indoor installation
Overvoltage Category	III
Ip Degree Of Protection	IP30 back: conforming to IEC 60529 IP50 front face: conforming to IEC 60529
Relative Humidity	5...95 %
Pollution Degree	2

Ambient Air Temperature For Operation	-4...158 °F (-20...70 °C)
Ambient Air Temperature For Storage	-40...185 °F (-40...85 °C)
Operating Altitude	0...6561.68 ft (0...2000 m)
Standards	IEC 61010-1
Width	7.56 in (192 mm)
Depth	6.85 in (174 mm)
Height	7.56 in (192 mm)
Net Weight	4.19 lb(US) (1.9 kg)

## Ordering and shipping details

Category	09755-POWERLOGIC ION 75/76 ACCESSORIES
Discount Schedule	PM1
Returnability	No

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
California Proposition 65	WARNING: Cancer and Reproductive Harm - <a href="#">www.P65Warnings.ca.gov</a>