


Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Range	AccuSine
Product or component type	Current transformer
Accessory / separate part category	Measurement accessory
Range compatibility	AccuSine PCS+ active harmonic filter AccuSine PFV+ electronic VAR controller
Current transformer type	Split core balance
Secondary current	5 A

Complementary

Current transformer ratio	5000/5
Electrical connection	Flying lead 3.65 m 720 V
Input impedance	1.8 Ohm
Line Rated Current	5000 A
Thermal factor	1.25 at θ 30 °C 1 at θ 55 °C
Network frequency	50...400 Hz
Measurement accuracy	1 %
Accuracy class	Class 1
System Voltage	< 720 V AC at 50...400 Hz
[Uimp] rated impulse withstand voltage	10 kV (50 μ s)
Depth	38.1 mm outside
Diameter	Inner : 203.2 mm Outer : 266.7 mm
Product weight	5.51 lb(US) (2.5 kg)

Environment

Standards	IEC 60044-1
-----------	-------------

Product certifications	CE cURus
Ambient air temperature for operation	-49...131 °F (-45...55 °C)
Ambient air temperature for storage	-49...392 °F (-45...200 °C)

Ordering and shipping details

Category	00089 - ACTIVE FILTERS
Discount Schedule	DE2C
GTIN	003606480892097
Nbr. of units in pkg.	1
Package weight(Lbs)	5.5
Returnability	N
Country of origin	US