

PCSPCTFCL50005R411

AccuSine+ current transformer - 5000/5 -
Rectangular Split Core - 168.3x279.4mm

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Range	AccuSine
Product or component type	Rectangular Current Transformer
Accessory / separate part category	Measurement accessory
Range compatibility	AccuSine PCS+ active harmonic filter AccuSine PFV+ electronic VAR controller
Current transformer type	Split core balance
Secondary current	5 A

Complementary

Current transformer ratio	5000/5
Electrical connection	Flying lead 3.65 m 720 V
Input impedance	1.8 Ohm
Line Rated Current	5000 A
Thermal factor	1.25 at θ 30 °C 1 at θ 55 °C
Network frequency	50...400 Hz
Measurement accuracy	1 %
Accuracy class	Class 1
System Voltage	< 720 V AC at 50...400 Hz
[Uimp] rated impulse withstand voltage	10 kV (50 μ s)
Width	165.1 mm outside 101.6 mm inner
Height	339.7 mm outside 279.4 mm inner
Depth	38.1 mm outside
Product weight	6.17 lb(US) (2.8 kg)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

Environment

Standards	IEC 60044-1
Product certifications	CE cURus
Ambient air temperature for operation	-49...131 °F (-45...55 °C)

Ordering and shipping details

Category	00089 - ACTIVE FILTERS
Discount Schedule	DE2C
GTIN	003606480892103
Nbr. of units in pkg.	1
Package weight(Lbs)	6.2999999999999998
Returnability	N
Country of origin	US