

# PGA36120U31A

## MOLDED CASE CIRCUIT BREAKER 600V 1200A

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 20,790.00 USD



### Main

Product or component type	Circuit breaker
Range of product	PowerPact P
Current sensor rating range	1200 A
Line Rated Current	1200 A
Breaking capacity	65 kA 240 V AC 35 kA 480 V AC 18 kA 600 V AC
AWG gauge	AWG 3/0...500 kcmil aluminium/copper 4(cable(s))
Trip unit technology	Electronic standard Micrologic 3.0 LI

### Complementary

Product certifications	UL listed CSA IEC
System Voltage	600 V AC
Module type	P-Frame
Mounting location	Busbar
Mounting mode	I-Line
Poles description	3P
Breaking capacity code	G
Electrical connection	I-Line connection line Lugs load
Continuous current rating	80 %
Device short name	A
Height	16.16 in
Depth	8.05 in
Width	8.27 in

Tightening torque	50 N.mFor 0.15...0.37 in <sup>2</sup> (95...240 mm <sup>2</sup> ) (AWG 3/0...500 kcmil) 1...1.3 N.m
-------------------	--

**Ordering and shipping details**

Category	01210 - PG,H,J,K,L,N I-LINE BREAKERS
Discount Schedule	DE2
GTIN	00785901550945
Nbr. of units in pkg.	1
Package weight(Lbs)	32
Returnability	Y
Country of origin	US

**Offer Sustainability**

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------