

Product data sheet

Specifications

SQUARE D



Active harmonic filter 300 amp 208-240 VAC N12 Enclosure

PCSP300D2N12

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 216,761.00 USD

Main

Range Of Product	AccuSine
Product Name	AccuSine PCS+
Product Or Component Type	Active harmonic filter

Complementary

Network Type	3P
Network Configuration	3 or 4 wires
Network Rated Voltage	208...240 V AC
Input Frequency	50/60 Hz +/- 3 Hz auto sensing
Maximum Permissible Voltage	1.1 x Un
Neutral Correction	Not provided
Rms Output Current Rating	300 A
Reactive Power Rating	124.7 kvar 240 V AC 50/60 Hz
Operating Modes	Power factor correction Harmonic cancellation Mains current balancing
Installation Location	Indoor
Enclosure Mounting	Floor-standing
Protection Type	Circuit breaker protection
Disconnect Type	Door-interlocked with rotary handle
Interrupt Capacity	200 kA
Heat Dissipation	Rear plenum with forced ventilation for high heat flow
Electromagnetic Compatibility	Conducted EMC, class A EN 61000-6-4
Accessibility For Operation	Front
Location Of Connection	Top or bottom

Environment

Enclosure Degree Of Protection	UL type 12
Environmental Characteristic	Operating 3C2 IEC 60721-3-3 Operating 3S2 IEC 60721-3-3 Storage 3C3 IEC 60721-3-3 Storage 3S3 IEC 60721-3-3
Operating Altitude	<= 3280.84 ft (1000 m) 1 % per 100 m

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	32...104 °F (0...40 °C) 32...122 °F (0...50 °C) maximum with current derating of 2 % per °C
Relative Humidity	0...95 %
Pcba Protection	Conformal coated
Standards	UL 508 EN 61000-6-4 CSA C22.2 No 60947-1-07 EN 60439-1 CSA C22.2 No 14 UL 60947-1
Product Certifications	cULus ABS RCM CE
Ambient Air Temperature For Storage	-4...140 °F (-20...60 °C)
Net Weight	892.87 lb(US) (405 kg)
Height	82.68 in (2100 mm)
Width	35.43 in (900 mm)
Color	Light gray RAL 7035)
Depth	23.62 in (600 mm)

Ordering and shipping details

Category	US1DE2C00089
Discount Schedule	DE2C
Gtin	3606489905613
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	91.77 in (233.1 cm)
Package 1 Width	47.01 in (119.4 cm)
Package 1 Length	47.01 in (119.4 cm)
Package 1 Weight	963.42 lb(US) (437.0 kg)

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

<div><div>✓</div><div>Toxic Heavy Metal Free</div></div>	
<div><div>✓</div><div>Mercury Free</div></div>	
<div><div>✓</div><div>Rohs Exemption Information</div></div>	<div>Yes</div>
<div>Eu Rohs Directive</div>	<div>Compliant</div> <div>EU RoHS Declaration</div>
<div>China Rohs Regulation</div>	<div>China RoHS declaration</div> <div>Product out of China RoHS scope. Substance declaration for your information.</div>
<div>Weee</div>	<div>The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.</div>
<div>California Proposition 65</div>	<div>WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov</div>