

PCSPCTFCL20005R

AccuSine+ current transformer - 2000/5 -
Rectangular Split Core - 69.8x168.2mm

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Range	AccuSine
Product or component type	Rectangular Current Transformer
Accessory / separate part category	Measurement accessory
Range compatibility	AccuSine PCS+ active harmonic filter AccuSine PFV+ electronic VAR controller
Current transformer type	Split core balance
Secondary current	5 A

Complementary

Current transformer ratio	2000/5
Electrical connection	Flying lead 3.65 m 720 V
Input impedance	1 Ohm
Line Rated Current	2000 A
Thermal factor	1.25 at θ 30 °C 1 at θ 55 °C
Network frequency	50...400 Hz
Measurement accuracy	1 %
Accuracy class	Class 1
System Voltage	< 720 V AC at 50...400 Hz
[Uimp] rated impulse withstand voltage	10 kV (50 μ s)
Width	139.7 mm outside 69.8 mm inner
Height	238 mm outside 168.2 mm inner
Depth	38.1 mm outside
Product weight	4.19 lb(US) (1.9 kg)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 60044-1
Product certifications	CE cURus
Ambient air temperature for operation	-49...131 °F (-45...55 °C)
Ambient air temperature for storage	-49...392 °F (-45...200 °C)

Ordering and shipping details

Category	00089 - ACTIVE FILTERS
Discount Schedule	DE2C
GTIN	003606480891885
Nbr. of units in pkg.	1
Package weight(Lbs)	4.410000000000001
Returnability	N
Country of origin	US