

# Product data sheet

Specifications



## AccuSine+ current transformer - 5000/5 - Round Split Core - diam: 203.2mm

PCSPCTFCL500058

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 4,881.26 USD

### Main

Range	AccuSine
Product Or Component Type	Current transformer
Accessory / Separate Part Category	Measurement accessory
Range Compatibility	AccuSine AccuSine PCS+ active harmonic filter AccuSine AccuSine PFV+ electronic VAR controller
Current Transformer Type	Split core
Shape	Round
Secondary Current	5 A

### Complementary

Current Transformer Ratio	5000/5
Electrical Connection	Flying lead 11.98 ft (3.65 m)720 V
Input Impedance	1.8 Ohm
Line Rated Current	5000 A
Thermal Factor	1.25 86 °F (30 °C) 1 131 °F (55 °C)
Network Frequency	50...400 Hz
Measurement Accuracy	1 %
Accuracy Class	Class 1
[Ue] Rated Operational Voltage	< 720 V AC 50...400 Hz
[Uimp] Rated Impulse Withstand Voltage	10 kV (50 µs)
Depth	Outside 1.50 in (38.1 mm)
Diameter	Inner 8.00 in (203.2 mm) Outer 10.50 in (266.7 mm)
Net Weight	5.51 lb(US) (2.5 kg)

### Environment

Standards	IEC 60044-1
Product Certifications	cURus CE
Ambient Air Temperature For Operation	-49...131 °F (-45...55 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	-49...392 °F (-45...200 °C)
-------------------------------------	-----------------------------

## Ordering and shipping details

Category	US1DE2C00089
Discount Schedule	DE2C
Gtin	3606480892097
Returnability	No
Country Of Origin	US

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.02 in (10.2 cm)
Package 1 Width	18.03 in (45.8 cm)
Package 1 Length	18.03 in (45.8 cm)
Package 1 Weight	5.50 lb(US) (2.495 kg)

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Toxic Heavy Metal Free

 Mercury Free

 Rohs Exemption Information [Yes](#)

**Eu Rohs Directive** Compliant  
[EU RoHS Declaration](#)

**China Rohs Regulation** [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information.

**Weee** The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

**California Proposition 65** WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)