



Overview

| | |
|----------------------|--|
| Description | Designed to increase flexibility and agility of data center power distribution through a design that does not require a raised floor. |
| Model Name | InfraStruxure PDU 60kW 600V/208V |
| Includes | Installation guide , User Manual |
| Standard Lead Time | Usually Ships within 3 Weeks |
| Product Distribution | Anguilla , Antigua And Barbuda , Argentina , Aruba , Bahamas , Barbados , Belize , Bermuda , Bolivia , Brazil , Canada , Chile , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Grenada , Guadeloupe , Guatemala , Guyana , French Guiana , Haiti , Honduras , Jamaica , Madagascar , Martinique , Mauritius , Mayotte , Mexico , Netherlands Antilles , Nicaragua , Panama , Paraguay , Peru , Puerto Rico , Reunion , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Trinidad And Tobago , Turks And Caicos Islands , United States , Uruguay , Venezuela , VIRGIN ISLANDS (UNITED STATES) |

Output

| | |
|--------------------------------------|----------------|
| Nominal Output Voltage | 120V , 208 3PH |
| Maximum Total Current Draw per Phase | 167 A |

Input

| | |
|--------------------------------|----------------|
| Nominal Input Voltage | 600 3PH |
| Input Frequency | 60 Hz +/- 3 Hz |
| Number of Power Cords | 1 |
| Maximum Line Current per phase | 58 A |

Physical

| | |
|-----------------|-------------------------|
| Net Weight | 1012.0 lbs (460.0 kg) |
| Maximum Height | 81.0 inches (2057.0 mm) |
| Maximum Width | 24.0 inches (610.0 mm) |
| Maximum Depth | 35.98 inches (914.0 mm) |
| Shipping Weight | 1034.0 lbs (470.0 kg) |
| Shipping Height | 86.0 inches (2184.0 mm) |
| Shipping Width | 36.0 inches (914.0 mm) |

| | |
|----------------|-------------------------|
| Shipping Depth | 48.0 inches (1219.0 mm) |
| Color | Black |

Environmental

| | |
|-----------------------------|------------------------------|
| Operating Environment | 32 - 104 °F (0 - 40 °C) |
| Operating Relative Humidity | 0 - 95 % |
| Operating Elevation | 0-3333 feet (0-999.9 meters) |
| Storage Temperature | 5 - 113 °F (-15 - 45 °C) |
| Storage Relative Humidity | 0 - 95 % |
| Storage Elevation | 0-30000 feet (0-9000 meters) |

Conformance

| | |
|-------------------|--------------------------|
| Approvals | UL 60950 |
| Standard warranty | 1 year repair or replace |