





Load center, QO, 1 phase, 24 spaces, 24 circuits, 125A convertible main lugs, NEMA3R, gnd bar, UL

QO124L125GRB



! Discontinued on: Sep 1, 2020

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Marketing Trade Name	QO	
Product Type	Load Center	
Enclosure Type	Weatherproof enclosure	
Cover Type	Surface cover	

Complementary

Tightening Torque	Main lugs 50 lb.in, AWG 6AWG 2/0, aluminium/copper	
Pon Convertible Mains (Lugs)	Convertible Mains (lugs)	
Rated Current	125 A	
Number Of Spaces	24	
Max Short Circuit Current Rating	65 kA	
Maximum Number Of Single Pole 24 Circuits		
Maximum Number Of Tandem Breakers	0	
Number Of Phases	1 phase	
Voltage Rating	120/240 V AC	
Wire Size	AWG 6AWG 2/0 aluminium/copper	
Ground Bar	Grounding bar included (not installed)	
Electrical Connection	Lugs	
Wiring Configuration	3-wire	
Busbar Material	Tin plated copper: busbar	
Enclosure Material	Welded galvannealed steel	
Surface Finish	Baked enamel Gray	
Box Number	4R	
Height	22.05 in (560 mm)	
Width	14.76 in (375 mm)	

Environment

Enclosure Rating NEMA 3R outdoor

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ambient Air Temperature For	23 °F (-5 °C)
Operation	104 °F (40 °C)
Product Certifications	UL Listed

Ordering and shipping details

Category	US1DE3A00002	
Discount Schedule	DE3A	
Gtin	785901867999	
Returnability	No	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	23.80 in (60.452 cm)	
Package 1 Width	5.20 in (13.208 cm)	
Package 1 Length	15.50 in (39.37 cm)	
Package 1 Weight	23.95 lb(US) (10.864 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov