

Product data sheet

Characteristics

QO124L125PGCMR

QO LoadCTR, Main Lug, 125A, 1PH-3W, 24SP, NEMA1, MR.,Incl.Gnd.Bar, PON, Comb.CV

Product availability : Stock - Normally stocked in distribution facility



Price** : 5,800.00 USD



Main

Product	Load Center
Marketing Trade Name	QO
Load center type	Main lugs
Line Rated Current	125 A
Number of spaces	24
Short Circuit Current Rating	65 kA
Maximum Number of Single Pole Circuits	24
Maximum Number of Tandem Breakers	0
Phase	1 phase
System Voltage	120/240 V AC

Complementary

Bus rated current	125 A
Wire Size	AWG 6...AWG 2/0 (copper or aluminium)
Number of Monitored Circuits	6 standard 18 maximum
Enclosure Rating	NEMA 1 indoor
Mounting mode	Flush-mounted Surface mounted
Cover type	Combination flush/surface cover
Electrical Connection	Feed-thru lugs
Wiring configuration	3-wire
Busbar Material	Tin plated aluminium busbar
Enclosure Material	Welded sheet steel
Cover Finish	Baked enamel white

Product compatibility	Solar ready Electric vehicle ready
Product certifications	UL listed
Height	531 mm
Width	14.25 in (362 mm)
Depth	3.74 in (95 mm)
Tightening torque	50 lbf.in AWG 6...AWG 2/0

Ordering and shipping details

Category	10003 - QO PON 1PH LC,12-60 CKT, ML N1
Discount Schedule	DE3A
GTIN	00785901518112
Nbr. of units in pkg.	1
Package weight(Lbs)	1
Returnability	Y
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1742 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov