Product data sheet

Specifications



() Discontinued

Load center, QO, 1 phase, 40 spaces, 40 circuits, 200A convertible main breaker, PoN, NEMA1, blank endwalls, UL

QO140M200PCBE

() Discontinued on: Jun 30, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| Marketing Trade Name | QO |
|----------------------|---------------------------------|
| Product Type | Load Center |
| Cover Type | Combination flush/surface cover |
| Provided Equipment | Cover |

Complementary

| Tightening Torque | Cover 20 lb.in |
|-------------------------------------------|---------------------------------|
| Pon Convertible Mains (Lugs) | PoN Convertible Mains (breaker) |
| Rated Current | 200 A |
| Number Of Spaces | 40 |
| Max Short Circuit Current Rating | 22 kA |
| Maximum Number Of Single Pole Circuits | 40 |
| Maximum Number Of Tandem Breakers | 20 |
| Number Of Phases | 1 phase |
| Box Number | 11 |
| Height | 37.99 in (965 mm) |
| Width | 14.25 in (362 mm) |
| Depth | 3.74 in (95 mm) |
| Net Weight | 33.62 lb(US) (15.250 kg) |
| | |

Environment

| Enclosure Rating | NEMA 1 indoor |
|------------------------------------------|---------------------------------|
| Ambient Air Temperature For Operation | 23 °F (-5 °C) 104 °F (40 °C) |
| Product Certifications | UL Listed |

Ordering and shipping details

| Category | US1DE3A10001 | |
|-------------------|--------------|--|
| Discount Schedule | DE3A | |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Gtin | 785901086086 |
|-------------------|--------------|
| Returnability | No |
| Country Of Origin | US |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|--------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 37.99 in (96.5 cm) |
| Package 1 Width | 14.25 in (36.2 cm) |
| Package 1 Length | 3.74 in (9.5 cm) |
| Package 1 Weight | 33.30 lb(US) (15.105 kg) |

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

| Toxic Heavy Metal Free | |
|----------------------------|-----|
| Mercury Free | |
| Rohs Exemption Information | Yes |

Certifications & Standards

| REACh Declaration |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Compliant |
| EU RoHS Declaration |
| China RoHS declaration |
| Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Product Environmental Profile |
| No need of specific recycling operations |
| WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| |