Product data sheet

Specifications







Circuit breaker, PowerPacT P, 800A, 3 pole, 600VAC, 25kA, I-Line, Micrologic 5.0P, 100%, ABC, modbus

PJA36080CU63AE1

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 30,566.00 USD

Main

Range	PowerPact	
Product Name	PowerPact P	
Product Or Component Type	Circuit breaker	
Device Application	Distribution	

Complementary

Complementary		
Line Rated Current	800 A	
Number Of Poles	3P	
Control Type	Toggle	
Breaking Capacity Code	J	
Breaking Capacity	AIR 100 kA 240 V AC 50/60 Hz UL 489 AIR 65 kA 480 V AC 50/60 Hz UL 489 AIR 25 kA 600 V AC 50/60 Hz UL 489 Icu 65 kA 240 V AC 50/60 Hz IEC 60947-2 Icu 50 kA 380/415 V AC 50/60 Hz IEC 60947-2	
[Ue] Rated Operational Voltage	600 V AC 50/60 Hz UL 489	
Network Frequency	50/60 Hz	
[Ics] Rated Service Breaking Capacity	35 kA 240 V AC 50/60 Hz IEC 60947-2 25 kA 380/415 V AC 50/60 Hz IEC 60947-2	
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947-2	
Trip Unit Technology	Electronic, power, MicroLogic 5.0 P, LSI	
Continuous Current Rating	100 %	
[Ui] Rated Insulation Voltage	750 V IEC 60947-2	
Trip Unit Name	MicroLogic 5.0 P	
Accessory / Separate Part Type	Modbus connecting cable	
Awg Gauge	3 x AWG 3/0500 kcmil aluminium/copper	
Local Signalling	Overload 1 1 LED amber) 1 flag green) Trip causes 4 trip indicator red)	
Mounting Mode	I-Line bracket)	
Mounting Support	Bracket	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Electrical Connection	I-Line connection, line	
	Lugs, load	
	•	
Terminal Identifier	AL800M23K	
Long Time Pick-Up Adjustment Range	0.41 x lr	
Mounting Height	9 in (228.60 mm)	
Tightening Torque	442.54 lbf.in (50 N.m) 0.150.37 in² (95240 mm²) (3 x AWG 3/0500 kcmil) 8.8511.51 lbf.in (1.01.3 N.m)	
Number Of Slots	2 auxiliary switch OF plug-in) 1 alarm switch SD plug-in) 1 overcurrent trip switch SDE plug-in) 1 voltage release MN or MX plug-in)	
Power Wire Stripping Length	0.98 in (25 mm)	
Height	12.86 in (326.64 mm)	
Width	8.27 in (210.06 mm)	
Depth	8.05 in (204.47 mm)	
Net Weight	32 lb(US) (14.51 kg)	
Quantity Per Set	1	
Phase Connection	ABC	
Communication Interface	Modbus	
Circuit Breaker Application	HACR rated	

Environment

Quality Labels	CE
Standards	UL CSA NEMA NOM-003-SCFI-2000 IEC 60947-2
Product Certifications	UL CSA NOM
Ip Degree Of Protection	Front cover IP40
Pollution Degree	3 IEC 60947-1
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)
Operating Altitude	< 6561.68 ft (2000 m) without derating 13123.36 ft (4000 m) with derating

Ordering and shipping details

Category	US10DE201210
Discount Schedule	0DE2
Gtin	3606486285381
Returnability	Yes

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	12.87 in (32.7 cm)
Package 1 Width	8.27 in (21.0 cm)
Package 1 Length	8.03 in (20.4 cm)
Package 1 Weight	32.00 lb(US) (14.515 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov