





# MINIATURE CIRCUIT BREAKER 277V 30A

QYU130

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 183.00 USD

#### Main

Product	Supplementary Protector
Range	QYU
Circuit Breaker Type	Standard

### Complementary

Current Rating	30 A
Voltage Rating	277 V AC
Mounting Type	Unit mount
Number Of Poles	1P
Short Circuit Current Rating	5 kA
Electrical Connection	Lugs
Wire Size	AWG 14AWG 2 aluminium/copper
Tightening Torque	45 lbf.in (5.08 N.m) (AWG 14AWG 2)

#### **Environment**

Certifications UL Recognized

#### Ordering and shipping details

Category	US10DE200900
Discount Schedule	0DE2
Gtin	785901586685
Returnability	Yes
Country Of Origin	US

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.00 in (7.62 cm)
Package 1 Width	0.75 in (1.9 cm)
Package 1 Length	4.06 in (10.302 cm)
Package 1 Weight	6.08 oz (172.365 g)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## **Contractual warranty**

Warranty

18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

#### Well-being performance

<b>⊘</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Halogen Free Product	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations