



Main

Range of product	Zelio Time
Product or component type	Electromechanical timing relay
Discrete output type	Relay
Contacts type and composition	1 NO instantaneous contact
Component name	RE88226
Time delay type	Function 3 Function 4 Function 2
Time delay range	0...12 h
[Us] rated supply voltage	220...240 V AC 50 Hz
Electrical connection	Screw-clamp terminals 1 x 0.5...2 x 2.5 mm ²
Nominal output current	5 A

Complementary

Voltage range	0.8...1 Un 131 °F (55 °C) IEC 60255-100
Repeat accuracy	+/- 1.5 % 0...12 h +/- 1.5 % 0...6 min +/- 1.5 % 0...60 min
Setting accuracy of time delay	+/- 2 % 0...12 h +/- 2 % 0...6 min +/- 2 % 0...60 min
Reset time	0.2 s
On-load factor	100 %
Power consumption in VA	3 VA 0.8
[Ui] rated insulation voltage	380 V AC VDE 0110 group C 440 V DC VDE 0110 group C
[Ith] conventional free air thermal current	6.3 A
Breaking capacity	5 A 230 V 0.41 10000 cycles
Fixing mode	Plug-in 8-pin socket
Net weight	0.41 lb(US) (0.185 kg)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 60529 VDE 0660 VDE 0110 VDE 0435 NF C 45250
Product certifications	UR CSA
Ambient air temperature for storage	-4...158 °F (-20...70 °C)
Ambient air temperature for operation	14...131 °F (-10...55 °C)
Environmental characteristic	Tropical environment IEC 60068-2-10 Standard environment
IP degree of protection	IP10 terminal block) IP40 enclosure)
Vibration resistance	4 gn 10...55 Hz)
Dielectric test voltage	2 kV IEC 60255-5 2 kV VDE 0435

Ordering and shipping details

GTIN	03389110281057
Package weight(Lbs)	0.40 lb(US) (0.180 kg)

Contractual warranty

Warranty	18 months
----------	-----------