

Product data sheet

Specifications



electromechanical timing relay - 0..30 h - 127..230 V AC - 2 C/O

RE88256513

 **Discontinued on:** Jul 1, 2020

 **Discontinued**

Main

Range Of Product	Zelio Time
Product Or Component Type	Electromechanical timing relay
Discrete Output Type	Relay
Contacts Type And Composition	timed contact
Component Name	RE88256
Time Delay Range	0...30 h
[Us] Rated Supply Voltage	127...230 V AC 50 Hz
Electrical Connection	Cable Tag connector

Complementary

Control Type	Manual reset front panel
Voltage Range	0.85...1.1 Un 131 °F (55 °C) IEC 60255-100
Setting Accuracy Of Time Delay	+/- 4 % of full scale 0...30 h
On-Load Factor	100 %
Power Consumption In Va	3.1 VA 0.8
[Ui] Rated Insulation Voltage	380 V AC VDE 0110 group C 440 V DC VDE 0110 group C
[Ith] Conventional Free Air Thermal Current	20 A
Breaking Capacity	16 A 230 V 0.41 10000 cycles
Mechanical Durability	10000000 cycles
Fixing Mode	Screw-on panel
Net Weight	0.54 lb(US) (0.245 kg)

Environment

Ambient Air Temperature For Storage	-40...176 °F (-40...80 °C)
Ambient Air Temperature For Operation	23...158 °F (-5...70 °C)
Ip Degree Of Protection	IP10 terminal block)
Vibration Resistance	4 gn 10...55 Hz)
Dielectric Test Voltage	2 kV IEC 60255-5 2 kV VDE 0435

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Gtin	3389110281163
------	---------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.95 in (7.5 cm)
Package 1 Width	3.35 in (8.5 cm)
Package 1 Length	3.74 in (9.5 cm)
Package 1 Weight	9.77 oz (277 g)

Contractual warranty

Warranty	18 months
----------	-----------