

# QO11224L125WGBP

## LOAD CENTER QO MLO 240V 125A 1PH BULK PK

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 338.00 USD



⚠ Discontinued

QO11224L125WGBP has not been replaced. Please contact your customer care center for more information.

### Main

Product	Load Center
Marketing Trade Name	QO
Load center type	Main lugs
Line Rated Current	125 A
Number of spaces	12
Short Circuit Current Rating	65 kA
Maximum Number of Single Pole Circuits	24
Maximum Number of Tandem Breakers	12
Phase	1 phase
System Voltage	120/240 V AC

### Complementary

Wire Size	AWG 6...AWG 2/0 (aluminium/copper)
Enclosure Rating	NEMA 1 indoor
Cover type	Order separately
Electrical Connection	Lugs
Grounding Bar	Grounding bar (ordered separately)
Electrical connection	Lugs
Wiring configuration	3-wire
Busbar Material	Tin plated copper busbar
Enclosure Material	Welded sheet steel
Cover Finish	Baked enamel grey
Box number	6
Type of packing	Bulk
Product certifications	UL listed

Height	17.91 in (455 mm)
Width	14.25 in (362 mm)

**Ordering and shipping details**

Category	00184 - MISC. QO 1PH LOAD CENTERS
Discount Schedule	DE3A
GTIN	00785901660866
Nbr. of units in pkg.	45
Package weight(Lbs)	20
Returnability	Y
Country of origin	US

**Offer Sustainability**

RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------