# Product data sheet

Specifications







Load center, QO, 1 phase, 24 spaces, 34 circuits, 125A convertible main breaker, PoN, NEMA1, UL

QO124M125P

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 897.00 USD

### Main

Marketing Trade Name	QO
Product Type	Load Center
Complementary	
Tightening Torque	Cover 20 lb.in
Pon Convertible Mains (Lugs)	PoN Convertible Mains (breaker)
Rated Current	125 A
Number Of Spaces	24
Max Short Circuit Current Rating	22 kA
Maximum Number Of Single Pole Circuits	34

Maximum Number Of Tandem Breakers	10
Number Of Phases	1 phase
Ground Bar	Grounding bar (ordered separately)
Box Number	7
Height	20.91 in (531 mm)
Width	14.25 in (362 mm)
Depth	3.74 in (95 mm)
Net Weight	19.00 lb(US) (8.620 kg)

#### **Environment**

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

## Ordering and shipping details

Category	US1DE3A10001
Discount Schedule	DE3A
Gtin	785901609544
Returnability	Yes

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Country Of Origin	US
Packing Units	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.74 in (9.5 cm)
Package 1 Width	14.25 in (36.2 cm)
Package 1 Length	20.91 in (53.1 cm)

Package 1 Weight 15.00 lb(US) (6.804 kg)

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov