


Product data sheet

Specifications

SQUARE D



Load center interior, QO, 1 phase, 32 spaces, 32 circuits, 100A convertible main breaker, NEMA1, UL

QO132M100I

Discontinued

Discontinued on: Mar 15, 2022

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Type	Load Center Interior
Marketing Trade Name	QO
Load Center Type	Main breaker
Rated Current	100 A
Number Of Spaces	32
Max Short Circuit Current Rating	22 kA
Maximum Number Of Single Pole Circuits	32
Maximum Number Of Tandem Breakers	0
Number Of Phases	1 phase
Voltage Rating	120/240 V AC

Complementary

Ground Bar	Grounding bar (ordered separately)
Busbar Material	Tin plated copper: busbar
Product Certifications	UL Listed

Environment

Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
---------------------------------------	---------------------------------

Ordering and shipping details

Category	US10DE500199
Discount Schedule	0DE5
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	10.00 lb(US) (4.536 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------