Product data sheet

Specifications



Replacement cover, QO, for 60 space load center, combination flush and surface, gray

QOC60UC

Product availability: Stock - Normally stocked in distribution facility

Price*: 116.00 USD

Main

Marketing Trade Name	QO
Product Type	Load Center Cover

Complementary

Cover Type	Combination flush/surface cover
Product Compatibility	For indoor load center
Surface Finish	Baked enamel Gray
Number Of Spaces	60
Height	42.13 in (1070.10 mm)
Width	15.44 in (392.18 mm)
Depth	0.7 in (17.78 mm)
Tightening Torque	Cover 2.3 N.m

Ordering and shipping details

Category	US1DE3A00156	
Discount Schedule	DE3A	
Gtin	785901997627	
Returnability	Yes	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.30 in (3.3 cm)
Package 1 Width	15.51 in (39.4 cm)
Package 1 Length	42.40 in (107.7 cm)
Package 1 Weight	14.95 lb(US) (6.781 kg)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations