

Product data sheet

Specifications



industrial timing relay - 3..30 s - type W - 24 V AC/DC - 1 C/O

RE8PD31B

Discontinued on: Dec 2, 2020

End-of-service on: Dec 31, 2020

Discontinued

Main

Range Of Product	Zelio Time
Product Or Component Type	Optimum industrial timing relay
Component Name	RE8
Time Delay Type	W
Time Delay Range	3...30 s
Sale Per Indivisible Quantity	10

Complementary

Discrete Output Type	Relay
Contacts Material	90/10 silver nickel contacts
Width Pitch Dimension	0.89 in (22.5 mm)
[Us] Rated Supply Voltage	24 V AC/DC 50/60 Hz
Voltage Range	0.9...1.1 Us
Connections - Terminals	Screw terminals, 2 x 1.5 mm ² flexible with cable end Screw terminals, 2 x 2.5 mm ² flexible without cable end
Maximum [Ie] Rated Operational Current	2 A DC-13 24 V 158 °F (70 °C) IEC 60947-5-1/1991 2 A DC-13 24 V 158 °F (70 °C) VDE 0660 3 A AC-15 24 V 158 °F (70 °C) IEC 60947-5-1/1991 3 A AC-15 24 V 158 °F (70 °C) VDE 0660 0.1 A DC-13 250 V 158 °F (70 °C) IEC 60947-5-1/1991 0.1 A DC-13 250 V 158 °F (70 °C) VDE 0660 0.2 A DC-13 115 V 158 °F (70 °C) IEC 60947-5-1/1991 0.2 A DC-13 115 V 158 °F (70 °C) VDE 0660
Minimum Switching Capacity	10 mA 12 V
Input Voltage	24 V Y1
Maximum Switching Current	10 mA Y1)
Input Compatibility	2-wire sensors DC with leakage current < 1 mA <164.04 ft (50 m) Y1
Marking	CE
Overvoltage Category	III IEC 60664-1
[Ui] Rated Insulation Voltage	250 V IEC 300 V CSA
Supply Disconnection Value	> 0.1 Uc
Operating Position	Any position without derating
Surge Withstand	2 kV IEC 61000-4-5 level 3
Power Consumption In Va	0.7 VA 24 V

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Maximum Power Consumption In W	0.5 W 24 V
Terminal Description	(15-16-18)OC_OFF (A1-A2)CO (Y1)UNUSED
Height	3.07 in (78 mm)
Width	0.89 in (22.5 mm)
Depth	3.15 in (80 mm)
Net Weight	0.24 lb(US) (0.11 kg)

Environment

Standards	EN/IEC 61812-1
Product Certifications	CSA UL GL
Ambient Air Temperature For Storage	-40...185 °F (-40...85 °C)
Ambient Air Temperature For Operation	-4...140 °F (-20...60 °C)
Relative Humidity	15...85 % 3K3 IEC 60721-3-3
Vibration Resistance	0.35 mm 10...55 Hz)IEC 60068-2-6
Ip Degree Of Protection	IP20 terminals) IP50 casing)
Pollution Degree	3 IEC 60664-1
Dielectric Test Voltage	2.5 kV
Non-Dissipating Shock Wave	4.8 kV
Resistance To Electromagnetic Fields	9.14 V/m (10 V/m) IEC 61000-4-3 level 3
Resistance To Fast Transients	2 kV IEC 61000-4-4 level 3
Disturbance Radiated/Conducted	CISPR 22 - class A CISPR 11 group 1 - class A

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1